

# SmartRack Mounting Rail Kit - enables 4-Post Rackmount Installation of select UPS Systems

MODEL NUMBER: 4POSTRAILKITHD



### Highlights

- Supports heavy UPS systems in 4-post rackmount applications
- Adjustable to any setting between 20.5 and 36 in.
- Square-hole rack attachment hardware is included
- Supports a UPS chassis up to 500 lbs (226.8 kgs)

### Package Includes

- Pair of expandable L brackets
- Attachment hardware

### Description

The 4POSTRAILKITHD is an adjustable rack-mount shelf system that supports heavy UPS systems in 4-post rack-mount applications. Includes one pair of expandable "L bracket" mounting rails to offer front-to-rear support of select rack-mount UPS systems or other heavy pieces of networking or power protection equipment with a 17.5-inch-wide rectangular chassis. A pair of expandable "L brackets" adjust to any setting between 20.5 and 36 inches. The kit includes mounting hardware compatible with square-hole racks. Supports up to 500 pounds (226.8 kilograms)

### Features

- An adjustable rackmount shelf system that supports heavy UPS systems in 4-post rackmount applications
- Includes one pair of expandable "L bracket" mounting rails to offer front-to-rear support of rackmount UPS systems
- Expandable "L brackets" adjust to any setting between 20.5 and 36 inches
- Includes mounting hardware compatible with square-hole racks
- Compatible with other heavy pieces of networking or power protection equipment with a 17.5-in. wide rectangular chassis
- Supports up to 500 lbs (226.8 kgs)

## Specifications

| OVERVIEW                 |                     |
|--------------------------|---------------------|
| UPC Code                 | 037332182999        |
| Accessory Type           | Rack-Mount Rail Kit |
| Accessory Class          | UPS Accessories     |
| PHYSICAL                 |                     |
| Material of Construction | Steel               |



Powering Business Worldwide



|                                     |                         |
|-------------------------------------|-------------------------|
| Shipping Dimensions (hwd / in.)     | 6.50 x 4.50 x 24.00     |
| Shipping Dimensions (hwd / cm)      | 16.51 x 11.43 x 60.96   |
| Shipping Weight (lbs.)              | 10.50                   |
| Shipping Weight (kg)                | 4.76                    |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000   |
| Weight Capacity - Stationary (kg)   | 227                     |
| Weight Capacity - Stationary (lbs.) | 500                     |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                         |
| Product Compliance                  | RoHS                    |
| <b>WARRANTY &amp; SUPPORT</b>       |                         |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.