

4-Post 1U Universal Adjustable Rack-Mount Shelf Kit for Wall-Mount Racks

MODEL NUMBER: 4POSTRAILKITWM



Rack rail kit adds 2 adjustable shelves to the mounting rails of a 19 in. 4-post wall-mount enclosure to support heavy UPS systems and other pieces of network or power protection equipment.

Description

The 4POSTRAILKITWM wall-mount rack shelf kit provides extra support for heavy UPS systems, PDUs or other rack-mount components that weigh 150 pounds or less. It includes two adjustable mounting rails that attach to the mounting rails of your EIA-standard 19-inch wall-mount enclosure. Constructed using cold-rolled steel with a durable powder-coated finish, this heavy-duty rack rail kit comes with mounting hardware compatible with square-hole racks.

The rails offer front-to-rear support for equipment with 17.5-inch-wide rectangular chassis. They also adjust to any setting between 14.5 and 23.5 inches and leave the rack's front and rear mounting holes free to attach equipment. Setup is hassle-free and saves money and time on installation. Threaded-hole rack installation is also supported with user-supplied mounting hardware.

Features

Additional Rack-Mount Shelf for Your Wall-Mount Rack

- 1U rack rail kit with maximum load capacity of 150 lb.
- Compatible with 19 in. wall-mount open frame racks and enclosures
- Expandable support rails offer front-to-rear support for equipment with 17.5 in. rectangular chassis
- Rails adjust to any setting between 14.5 and 23.5 in.
- Leaves front and rear mounting holes free for equipment

Heavy-Duty Construction with Versatile Mounting Options

- Cold-rolled steel construction with powder-coated finish designed for long life
- Mounting hardware included for quick installation in square-hole rack

Highlights

- 1U rack rail kit with maximum load capacity of 150 lb.
- Compatible with mounting depths of 14.5–23.5 in.
- Leaves front and rear mounting holes free for equipment
- Made from cold-rolled steel with powder-coated finish
- Mounting hardware included for installation in square-hole rack

Package Includes

- Left rail piece, short
- Left rail piece, long
- Right rail piece, short
- Left rail piece, long
- (12) M6 screws
- (12) M6 washers
- Owner's manual



- Threaded-hole rack installation supported with user-supplied hardware

Specifications

OVERVIEW	
UPC Code	037332206374
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / cm)	5.59 x 4.83 x 54.10
Shipping Dimensions (hwd / in.)	2.20 x 1.90 x 21.30
Shipping Weight (kg)	1.36
Shipping Weight (lbs.)	3.00
Unit Dimensions (hwd / cm)	4.37 x 3.78 x 36.83-59.69
Unit Dimensions (hwd / in.)	1.72 x 1.49 x 14.5-23.5
Unit Weight (kg)	1.18
Unit Weight (lbs.)	2.6
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>