

# Eaton 72V Extended Battery Module (EBM) for 5PX2000RT3UNG2, 5PX3000RT3UNG2 UPS Systems, 3U Rack/Tower

MODEL NUMBER: 5PXEBM72RT3UAG2



Extended battery pack provides extended runtime for compatible UPS systems in small business, education, retail, financial or healthcare applications.

## Features

### Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The 5PXEBM72RT3UAG2 offers extended battery runtime when used in conjunction with Eaton's 5PX2000RT3UNG2 and 5PX3000RT3UNG2 5PX G2 UPS systems. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

### Supports 3U Rack or Tower Installation

This backup battery pack's multi-use form factor supports mounting in 3U of space in EIA-standard 19-inch open frame racks or enclosures using the included 4-post rail kit and mounting brackets. Tower stands are also included for optional upright configuration.

## Highlights

- Connects to select expandable Eaton 5PX G2 UPS systems for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Includes heavy-gauge cabling with high-current 72V DC connectors
- Supports 3U rack mounting or upright tower installation using included accessories

## System Requirements

Compatible only with Eaton's 5PX2000RT3UNG2 and 5PX3000RT3UNG2 5PX G2 UPS systems

## Package Includes

- 5PXEBM72RT3UAG2 External 72V Battery Pack
- External battery cable
- Rack-mounting hardware
- Tower support stands
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	743172105769
INPUT	
Input Phase	Single-Phase
OUTPUT	
Output Capacity (Watts)	3000
BATTERY	



Powering Business Worldwide

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	72
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/Eaton-Internal-Replacement-Battery-5PXEBM72RT3UAG2-EBM-744-A3125">744-A3125</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
<b>PHYSICAL</b>	
Color	Black
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Minimum Required Rack Depth (cm)	55.88
Minimum Required Rack Depth (inches)	22
Unit Dimensions (hwd / in.)	5.100 x 17.200 x 19.000
Unit Weight (lbs.)	87.500
Unit Weight (kg)	39.69
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed
Product Compliance	CE (Europe); REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.