



Powering Business Worldwide

Eaton Internal Replacement Battery Cartridge (RBC) for Select 1500VA UPS Systems and EBMs

MODEL NUMBER: 744-A3297



UPS backup battery cartridge replaces the expired or aging internal battery in your Eaton 9PX or SmartOnline UPS system or EBM.

Features

UPS Replacement Battery Cartridge for Select Eaton 9PX UPS Systems

This UPS backup battery replacement is compatible with Eaton's SU1500RTXLCD2U, SU1500RTXLCDN, 9PX1500RT, 9PX1500RTN and 9PX1500GRT UPS systems, as well as BP48RT and 9PXEBM48RT extended battery modules (EBMs). Eaton UPS batteries have an expected lifespan of three to five years, so you should take proactive steps to avoid a dead battery and ensure continuous uptime.

Comes Pre-Wired for Quick, Easy Installation

The sealed lead acid (SLA) 744-A3297 internal battery cartridge is hot-swappable, allowing you to install it without powering down any connected equipment. Built to function in a wide range of operating temperatures, the 744-A3297 has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. It is leakproof, requires no maintenance and comes pre-wired for quick and easy installation in your UPS system.

Specifications

OVERVIEW	
UPC Code	743172089762
INPUT	
Input Phase	Single-Phase
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Battery Replacement Description	Re-use existing wiring harness
Hot Swap Battery	Yes

Highlights

- Replacement battery backup for select Eaton 1.5kVA UPS and EBMs
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery cartridge requires no regular maintenance
- Ships ready for immediate UPS installation to prevent downtime

System Requirements

Compatible with SmartOnline SU1500RTXLCD2U (2023 redesign) and SU1500RTXLCDN (2023 redesign), as well as 9PX1500RT, 9PX1500RTN and 9PX1500GRT UPS systems as well as BP48RT and 9PXEBM48RT EBMs.

Package Includes

744-A3297 Internal Replacement Battery Cartridge



Powering Business Worldwide

PHYSICAL	
Unit Dimensions (hwd / in.)	4.000 x 14.000 x 10.000
Unit Weight (lbs.)	23.1
Unit Weight (kg)	10.48
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
APPLICATIONS	
Used With	9PX1500RT, 9PXEBM48RT, 9PX1500GRT, 9PX1500RTN, SU1500RTXLCD2U (2023 redesign), SU1500RTXLCDN (2023 redesign), BP48RT
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	FCC (USA); CE (Europe)

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.