



Powering Business Worldwide

Eaton Internal Replacement Battery Cartridge (RBC) for 5P750RC UPS Systems, TAA

MODEL NUMBER: 744-A4058



UPS backup battery cartridge replaces the expired or aging internal battery in your Eaton 5P UPS system.

Features

UPS Replacement Battery Cartridge for Select Eaton 5P UPS System

This UPS backup battery replacement is compatible with Eaton's 5P750RC UPS system. Eaton UPS batteries have an expected lifespan of three to five years, so you should take proactive steps to avoid a dead battery and ensure continuous uptime.

Comes Pre-Wired for Quick, Easy Installation

The sealed lead acid (SLA) 744-A4058 internal battery cartridge is hot-swappable, allowing you to install it without powering down any connected equipment. Built to function in a wide range of operating temperatures, the 744-A4058 has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. It is leakproof, requires no maintenance and comes pre-wired for quick and easy installation in your 5P UPS system.

Specifications

| OVERVIEW | |
|---------------------------------|----------------------------------|
| UPC Code | 743172089687 |
| INPUT | |
| Input Phase | Single-Phase |
| BATTERY | |
| Battery Type | Valve Regulated Lead Acid (VRLA) |
| Battery Replacement Description | Re-use existing wiring harness |
| Hot Swap Battery | Yes |
| PHYSICAL | |

Highlights

- Replacement battery backup for Eaton 5P750RC 5P UPS system
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery cartridge requires no regular maintenance
- Ships pre-wired and ready for immediate installation to prevent downtime

System Requirements

Compatible only with Eaton's 5P750RC UPS system

Package Includes

744-A4058 Internal Replacement Battery Cartridge



Powering Business Worldwide

| | |
|-----------------------------------|---|
| Unit Dimensions (hwd / in.) | 4.000 x 14.000 x 10.000 |
| Unit Weight (lbs.) | 11.4 |
| Unit Weight (kg) | 5.17 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| APPLICATIONS | |
| Used With | 5P750RC |
| STANDARDS & COMPLIANCE | |
| Product Certifications | UL Listed; cUL Listed |
| Product Compliance | RoHS; FCC (USA); Trade Agreements Act (TAA) |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.