


DataShield In-Line Surge Protector for Network and Phone Lines, 2-Line RJ11/RJ45

MODEL NUMBER: DTEL2



Highlights

- RJ11/RJ45 2-line dial-up surge protector
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

Package Includes

- DTEL2 dataline protector
- 5-in. RJ11 telephone patch cable
- Warranty information and instruction manual

Description

Tripp Lite's DTEL2 surge suppressor is designed to protect data and communications equipment against AC transients caused by lightning, electrostatic discharge and ground surges that can enter equipment from the signal lines or chassis ground. The DTEL2 features RJ45/RJ11 plugs for modems, telephone lines and answering or fax machines.

Features

- Protects against the effects of electrostatic discharge, faulty wiring and lightning
- Comes with RJ11 telephone patch cable

Specifications

MODEL TEXT	
Key Benefit	Your network/phone line is vulnerable to surges and power problems. These connections provide one more entry-way for transient surges to damage your equipment. Seal off your equipment from potential damage by stopping transient surges with the DataShield™ DTEL2 Network Surge Suppressor. It protects up to 2 network or phone lines, modems, fax machines and answering machines against damage from lightning, electrostatic discharge and ground surges.
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	250
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Connection Type	RJ11/RJ45
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Right-Angle Plug	0
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	260
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
Additional Dataline Protection	4,5 & 3,6 pairs
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>