

HDMI Splitter, 4-Port

MODEL NUMBER: **B118-304-R**



Description

Tripp Lite's HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device, to be displayed on multiple HDMI or DVI-D Single Link monitors. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Up to 64 displays can be connected by cascading up to three levels of additional splitters. Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the splitter; up to 25 ft. (7.62 m.) between the splitter and a monitor. Splitters can be located up to 100 ft. away from the source using a combination of Tripp Lite long length HDMI cables ([P568-050](#), [P568-100-HD](#) and a HDMI Signal Booster [B122-000-60](#) or [B123-001-60](#)). Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Supports 3D, Lip-Sync Pass Through, and CEC Pass Through
- Connects to both HDMI and DVI-D Single-Link displays
- Cascade up to three levels of splitters to support up to 64 displays
- Locate a monitor up to 41 ft. (12.5 m.) from a HDMI source; up to 16 ft. (5 m.) between the source and the switch; up to 25 ft. (7.62 m.) between the switch and a monitor
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- HDCP compliant
- Connects to both HDMI and DVI-D Single-Link displays
- ATC certified
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 16 ft. (5 m.), unless using a signal booster ([B122-000-60](#) or [B123-001-60](#))
- The cable connecting the splitter to a HDMI monitor must be no longer than 25 ft. (7.62 m.)

Package Includes

- B118-304-R 4-Port HDMI Splitter
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Mounting Hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Ports	4
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(4) HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>