

## Remote Control Module for Tripp Lite Pure Sine-Wave Inverter/Chargers

MODEL NUMBER: APSRMSW



Gives you complete control of your Tripp Lite pure sine-wave inverter/charger from up to 32 ft. away. Ideal for automotive, remote site, industrial, commercial and residential applications.

### Description

The APSRMSW Remote Control Module lets you monitor and control your Tripp Lite APS1012SW, APS2012SW, APSX1012SW or APSX2012SW sine-wave inverter/charger from up to 32 feet away. Ideal for automotive, remote site, industrial, commercial and residential applications, the APSRMSW mounts easily on a fixed, flat surface, so you can control your inverter/charger from the comfort of your vehicle.

Monitor battery status, charger status and power conditions at a glance via the front-panel LEDs. The molded plastic housing also includes an on/off button that gives you instant one-touch control of the connected inverter/charger. Built-in mounting slots and a 32-foot cable provide plenty of flexibility in mounting and operating the APSRMSW. A faceplate is included for front-panel mounting in an RV, boat or other vehicle.

### Features

#### Control Your Inverter/Charger Up to 32 Ft. Away

- Ideal for automotive, remote site, industrial, commercial and residential applications
- Allows complete remote monitoring and control of Tripp Lite APS1012SW, APS2012SW, APSX1012SW and APSX2012SW sine-wave inverter/chargers

#### Intuitive Front Panel Indicators

- LEDs show battery status, charger status and power conditions at a glance
- On/off button for one-touch control of connected inverter/charger

#### Built-In Mounting Slots

- Installs in variety of locations and configurations, including front-panel, rear-panel and below-dashboard
- Molded plastic housing
- Faceplate included for front-panel mounting

### Highlights

- LEDs indicate battery and power status at a glance
- On/off button for instant one-touch control
- Suited for front-panel, rear-panel or below-dash mounting
- Molded plastic housing
- Attractive faceplate for front-panel installation

### Package Includes

- APSRMSW Remote Control Module
- Faceplate
- Remote control cord, 32 ft.
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332163769
Accessory Type	Remote Control Module
Accessory Class	Power Inverter Accessories
INPUT	
Voltage Compatibility (VDC)	0
OUTPUT	
Pure Sine Wave Output	No
Nominal Output Voltage(s) Supported	120V
Output Receptacles	5-15R
Continuous Output Capacity (Watts)	0
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Battery Charge and Operational LEDs
Switches	Remote Control Switch
PHYSICAL	
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	2.71 x 4.41 x 6.61
Shipping Dimensions (hwd / cm)	6.88 x 11.20 x 16.79
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	3.860 x 1.890 x 0.850
Unit Dimensions (hwd / cm)	9.80 x 4.80 x 6.61
Unit Weight (lbs.)	1.00
Unit Weight (kg)	0.45
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.