

## 8-Port KVM Switch, 1U Rack-Mount, On-Screen Display

MODEL NUMBER: **B007-008**



### Description

Tripp Lite's 8-port KVM Switch is the optimal solution for controlling up to 8 computers from one keyboard, mouse and monitor. Multiple KVM switches can be cascaded together in order to control up to 512 computers. Easily switch ports using the On Screen Display (OSD), keyboard hot key commands or push buttons. Also supports ultra-high 180MHz video resolutions up to 1920 x 1440 pixels without noticeable degradation. Innovative design adjusts to either rack-mount or stacking installation... rack-mount hardware included. Compatible with all major operating systems except Mac and Sun. Constructed of heavy-duty steel housing.

### Features

- Control up to 8 computers from a single keyboard, mouse, and monitor
- Control up to 512 computers by cascading additional B007-008 KVM switches
- Includes hardware for 1U mounting in a 19 in. rack
- Supports video resolutions up to 1920 x 1440
- Supports VGA, SVGA, or Multisync monitor
- No software or complicated set-up procedures required
- Switch between ports via OSD, pushbuttons, or keyboard hot key commands
- Includes autoscan feature
- Password security ensures that only authorized people have access to the connected computers
- Keyboard and mouse emulation for dependable computer boot-up; works on all operating systems
- Compatible with most mice, including scrolling mice
- 2 LEDs per port: one indicating the computer is connected and powered-on, and the other indicating the computer has the KVM focus
- Compatible with all major operating systems except Mac and Sun
- Constructed of heavy-duty steel housing

### Highlights

- Ultra-compact--occupies only 1U rack space
- Does not require software or complicated setup--simply plug and play
- Can be placed virtually anywhere (no AC power required)
- Adapts to rack, stack under-monitor or desktop applications
- Rack-mount hardware included

### System Requirements

- PS/2 mouse and keyboard
- PS/2 or USB computer (B015-000 PS/2 to USB adapter required for USB computers)
- 1 P753-Series PS/2 KVM cable kit for each connected computer
- Compatible with all major operating systems except Mac and Sun

### Package Includes

- 8-Port KVM Switch (rackmount ready)
- Interlocking feet (for non-rackmount applications).
- Optional AC power adapter
- User manual

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332043573
Console	No
Max CPU	512
Product Rear View	B007-008-rear.pdf
Technology	PS/2; VGA/SVGA
<b>PHYSICAL</b>	
Color	Black
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	6.00 x 22.50 x 10.00
Shipping Dimensions (hwd / cm)	15.24 x 57.15 x 25.40
Shipping Weight (lbs.)	8.00
Shipping Weight (kg)	3.63
<b>ENVIRONMENTAL</b>	
BTUs	50Hz, 8.9 / 60Hz, 8.5
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes
<b>CONNECTIONS</b>	
Number of Ports	8
PC/Server Connections	VGA; USB; PS/2
<b>FEATURES &amp; SPECIFICATIONS</b>	
NIAP-Certified Secure	No
Number of Users	1
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.