

## NetDirector USB Server Interface Unit with Virtual Media Support and Audio (B064-IPG Series), TAA

MODEL NUMBER: **B055-001-USB-VA**



Connects a server's audio, video and USB mouse/keyboard ports to a compatible Tripp Lite B064-Series NetDirector KVM switch up to 164 ft. away using Cat5e/6 cabling.

### Description

The B055-001-USB-VA NetDirector® USB Server Interface Unit connects a server or computer with HD15 VGA video, 3.5 mm audio and USB mouse/keyboard ports to a compatible B064-IPG Series KVM switch. Using Cat5e/6 cabling, you can locate the KVM switch up to 164 feet (50 meters) from the server.

Allowing the server to access the KVM switch's Virtual Media functionality via low-cost Cat5e/6 cable eliminates the need for bulky KVM cables. This frees up precious space in your server cabinet, and allows for better ventilation and longer cable runs. Running cable through conduit and other tight spaces takes advantage of the increased flexibility when setting up your network application.

No software or external power supply is needed. The unit's compact, lightweight design is plug-and-play for immediate installation and deployment. It complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Note: SIUs that were purchased prior to that of your KVM switch may require a firmware upgrade in order for them to work properly (see Maintenance under OSD Operation section of your B064-Series KVM Owner's Manual for details)

### Features

#### Convenient, Cost-Effective KVM Connection

- Connects USB server to B064-IPG NetDirector KVM switch via Cat5e/6 cable
- Allows server to access Virtual Media functionality
- Features HD15 VGA, 3.5 mm audio and USB male and RJ45 female connectors
- Maximum distance between server and KVM switch of 164 ft.

#### Eliminates Bulky KVM Cables

- Frees precious space in server cabinet
- Provides better ventilation and longer cable runs
- More flexibility for running cable through conduit and other tight spaces

#### Plug-and-Play Convenience

- No software or external power supply required

### Highlights

- Provides connected USB server with Virtual Media access
- Includes HD15 VGA, 3.5 mm audio, USB and RJ45 connectors
- Eliminates thick, heavy KVM cable kits
- Ideal for running cable through conduit and other tight spaces
- Plug-and-play—no software or power supply required

### System Requirements

- Server or CPU with HD15 and USB ports
- B064-IPG Series NetDirector KVM switch
- Cat5e/6 cable

### Package Includes

- B055-001-USB-VA NetDirector USB Server Interface Unit



Powering Business Worldwide

TRIPP LITE  
SERIES

- Ready for immediate installation and deployment

**TAA-Compliant**

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Specifications

OVERVIEW	
UPC Code	037332199751
Accessory Type	Server Interface Unit
Technology	Cat5/5e; VGA/SVGA
Accessory Class	KVM Switch Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.70 x 5.00 x 4.90
Shipping Dimensions (hwd / cm)	4.32 x 12.70 x 12.45
Shipping Weight (lbs.)	0.38
Shipping Weight (kg)	0.17
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.