


# SmartRack 1U Rack-Mount Device Rack Extension Bracket, 1.5 in.

MODEL NUMBER: B018-000-1P5



### Highlights

- Extends 1.5 in. past the front vertical mounting rails
- Made from cold-rolled steel with black powder-coated finish
- Compatible with EIA-standard 19 in. racks and rack cabinets
- All necessary mounting hardware is included

### Package Includes

- (2) Rack extensions
- (8) M6 screws
- (8) M6 cage nuts
- (8) M6 cup washers
- Installation guide

1U rack extensions allow you to fully open your console or console KVM switch when equipment mounted just above it extends past the front rails and prevents the unit from opening.

### Description

The B018-000-1P5 1U Rack-Mount Device Rack Extension Bracket allows you to mount a console or console KVM switch into a rack so that it extends 1.5 inches past the front vertical mounting rails. This is of use when the rack equipment mounted just above the console protrudes out the front of the rack and prevents the console from fully opening. The rack-mount extension brackets are constructed from cold-rolled steel with a black powder-coated finish to match your rack. Attach the rack extension brackets to your EIA-standard 19-inch rack, then attach the console or console KVM switch to the brackets. All necessary mounting hardware is included.

### Features

#### Extend Your Rack-Mount Device Past the Front Mounting Rails

- Allows your console or console KVM to fully open when it is being blocked by protruding rack equipment mounted just above it
- Extends 1.5 in. past the front vertical mounting rails
- Cold-rolled steel construction with black powder-coated finish designed for long life
- Compatible with EIA-standard 19 in. racks and rack cabinets
- All necessary mounting hardware is included

## Specifications

OVERVIEW	
UPC Code	037332206244
Accessory Type	Mounting Bracket; Rackmount Kit
Accessory Class	Rack Accessories
VIDEO	



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

3D Video Supported	No
<b>INPUT</b>	
Bus Powered	No
<b>POWER</b>	
Power Over Cable (PoC) Support	No
<b>PHYSICAL</b>	
Color	Black
Rackmountable	No
Shipping Dimensions (hwd / in.)	1.77 x 3.34 x 1.77
Shipping Dimensions (hwd / cm)	4.50 x 8.48 x 4.50
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
Unit Packaging Type	Box
<b>COMMUNICATIONS</b>	
EDID Compatible	No
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
10/100 Ethernet Extension Support	No
IP68 Rated	No
IP20 Rated	No
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.