

PS/2 Console Interface Module for NetDirector Matrix KVM Switches

MODEL NUMBER: **B062-002-PS2**



Description

Tripp Lite's PS/2 Console Interface Module allows a user to access a B060-Series NetDirector Matrix KVM Switch from as far away as 500 ft. The console (keyboard, monitor and mouse) is connected to the HD15 port and (2) PS/2 ports on the unit. The B062-002-PS2 is then connected to a B060-Series NetDirector Matrix KVM Switch via ordinary CAT5e cable.

The unit also includes a 3-in-1 PS/2 KVM Cable kit for connecting to a local computer/server. Simply use the switch on the front of the box to toggle between PC use and KVM switch use...no need to set up a separate console station.

Features

- Access a B060-Series NetDirector Matrix KVM switch from up to 500ft away
- Built-in KVM Switch for additional PC/server control
- Connects to KVM switch via inexpensive Cat5e patch cables
- Compact, space saving design
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

Highlights

- Needed to connect a console (PS/2 Keyboard, PS/2 Mouse and HD15 Monitor) to a B060-Series NetDirector Matrix KVM Switch via Cat5e cable
- Connects to KVM Switch from up to 500 ft. away
- Module features a built-in KVM Switch for additional PC/server control
- Small footprint design takes up very little space on the desktop
- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

System Requirements

- PS/2 keyboard, PS/2 mouse and monitor with a HD15 port
- A B060-Series NetDirector Matrix KVM Switch
- Cat5e/6 cable; up to 500ft

Package Includes

- 1 PS/2 Console Interface Module with Built-in KVM Switch
- External power supply with NEMA 1-15P Plug (Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A)
- 3-in-1 PS/2 KVM Cable Kit

Specifications

OVERVIEW	
UPC Code	037332134097
Accessory Type	Server Interface Unit
Technology	Cat5/5e; PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
POWER	
AC Adapter	Input: 100-240V, 0.8A, 27-34VA, 50/60Hz Output: DC 5V, 2.6A

CONNECTIONS	
Computer/Server Ports	1
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	(x2) MiniDIN6 (Male)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.75 x 10.50 x 8.75
Shipping Dimensions (hwd / cm)	9.52 x 26.67 x 22.22
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.