

2-Port DisplayPort to VGA Splitter, TAA

MODEL NUMBER: **B157-002-VGA**



Converts and splits a DisplayPort video signal for display on two VGA monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms.

Description

The B157-002-VGA 2-Port DisplayPort to VGA Splitter converts and splits a DisplayPort video signal for display on two VGA-enabled monitors, projectors or televisions at the same time. Ideal for offices, conference rooms, retail settings, trade shows and classrooms, this compact splitter features a built-in DisplayPort cable that connects to the source. It lets you use your existing VGA displays instead of buying new DisplayPort monitors or docking stations.

The B157-002-VGA supports video resolutions up to 1920 x 1080 (1080p) at 60 Hz, as well as HDCP, EDID and DDC. Orange LEDs next to each output port indicate whether the splitter is powered on and transmitting a signal to the connected displays. The splitter works with all operating systems and is small enough to carry in your backpack or computer bag. Plug-and-play convenience means no software or drivers are needed. An included USB Micro-B cable connects between the source and the splitter to provide power, so no external power supply is required.

Features

Converts and Splits DisplayPort Signal to 2 VGA Displays Simultaneously

- Ideal for offices, conference rooms, trade shows and classrooms
- Built-in DisplayPort cable connects to source
- Included USB Micro-B cable supplies power to splitter
- Save money on new DisplayPort displays or docking stations

Top-Shelf Performance

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Complies with HDCP, EDID and DDC

Highlights

- Supports video resolutions up to 1920 x 1080 @ 60 Hz
- Included USB Micro-B cable supplies power to unit
- Works with all operating systems
- Compact enough for easy carrying in backpack or laptop bag
- Plug and play—no software or drivers required

Package Includes

- B157-002-VGA 2-Port DisplayPort to VGA Splitter
- USB Micro-B cable, 3 ft.
- Owner's manual



- LEDs indicate whether splitter is powered on and transmitting signal to connected displays

Easy to Use Almost Anywhere

- Works with all operating systems
- Plug and play—no software, drivers or external power supply required
- Compact unit fits easily in backpack or computer bag

Specifications

OVERVIEW	
UPC Code	037332191496
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	4.32 x 20.07 x 14.22
Shipping Dimensions (hwd / in.)	1.70 x 7.90 x 5.60
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
CONNECTIONS	
Ports	2
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	VGA/SVGA; DisplayPort
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>