

Serial over Cat5/Cat6 RS232 Extender, Transmitter and Receiver, Up to 3280 ft. (999.74 m), TAA

MODEL NUMBER: **B165-101**



Description

Tripp Lites B165-101 RS232 Serial over Cat5 Extender Kit is a low cost solution that provides remote access and control of any RS232 protocol device. The B165-101 extends control of a serial device to over 3280-ft. (999.74 m). Supports full-duplex, 3 pin, data communication (signal ground, transmit data line, and receive data line). Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Locates an RS-232 Serial device up to 1,000 Meters from your system
- Supports full-duplex, 3 pin, data communication (signal ground, transmit data line, and receive data line)
- No software or drivers required...Plug-n-Play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Supported Baud Rates: 110, 1200, 9600, 19200, 38400, 57600, 115200 (max)

Specifications

OVERVIEW	
UPC Code	037332155474
AC Adapter	(x2) Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
Technology	Serial (RS232)
PHYSICAL	

Highlights

- Locates an RS-232 Serial device up to 3280-ft. (999.74 m) from your system
- Supports full-duplex, 3 pin, data communication (signal ground, transmit data line, and receive data line)
- No software or drivers required...Plug-n-Play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B165-101 Local Transmitter Unit
- B165-101 Remote Receiver Unit
- 2 External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 21.08
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 8.30
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
CONNECTIONS	
Ports	1
Side A - Connector 1	DB9 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	DB9 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>