

Switch - Reversible 4 Position IEEE Autoswitch

MODEL NUMBER: B170-004-R



Description

Very versatile. Use with any printer including a high speed IEEE1284 printer. Automatic switch can be used to share a printer between up to 4 PCs. Will automatically manage print jobs in a transparent manner. Switch can also be used to connect a PC to up to 4 printers. Target printer is selected via software (supplied) or manually. LEDs provide switch status at a glance. This compact unit does not require AC power allowing it to be located virtually anywhere. Connect switch to PC using an IEEE Switchbox cable (P710-010). Printer connects to switch using an IEEE printer cable (P606-006). Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- IEEE1284 Approved.
- Designed for use with all printers including IEEE high speed printers.
- Reversible: Connect 1 PC to up to 4 Printers or up to 4 PCs to 1 Printer.
- No AC required.
- Has both Automatic and Manual mode.
- Status LEDs quickly identify the mode as well as the port in use.
- Compact design enable switch to be located almost anywhere.
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Specifications

OVERVIEW		
UPC Code	037332014306	
Host Connector	USB A (MALE)	
CONNECTIONS		
Number of Ports	4	
Side A - Connector 1	DB25 (FEMALE)	

Highlights

- · Automatic, hands-free switching
- No external power source required
- Reversible design allows multiple computers to share 1 printer or 1 computer to use multiple printers
- Retail packaging

System Requirements

- Computer with a parallel port
- Parallel printer (either IEEE or non-IEEE)
- CD drive in the computer to load the driver
- One straight through IEEE switch cable per computer (model # P710-010)
- One parallel IEEE printer cable per printer (P606-006 or P606-010)

Package Includes

- B170-004-R Reversible 4 Position IEEE Autoswitch
- CD with Drivers
- Manual



Side B - Connector 1	(4) DB25 (FEMALE)	
PHYSICAL		
Color	Black	
Shipping Dimensions (hwd / in.)	9.00 x 4.25 x 1.50	
Shipping Dimensions (hwd / cm)	22.86 x 10.80 x 3.81	
Shipping Weight (lbs.)	0.70	
Shipping Weight (kg)	0.32	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.