

USB-Over-Cat5 Wall Plate Extender Kit

MODEL NUMBER: B202-150-WP



Highlights

- Locate USB peripherals up to 150 feet away from your computer
- Provides a finished look
- Uses readily available Cat5/Cat6 cable
- Bus Powered - no additional AC adapters required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Local Unit Wall plate
- Remote Unit Wall plate
- Wall plate Screws
- Manual

Description

Tripp Lite's USB over Cat5 Wall Plate Extender Kit allows you to connect your computer to USB peripherals up to 150 feet away from the host computer, over ordinary Cat5/Cat5e/Cat6 cable. The Transmitter and Receiver kit is Bus-powered, so no additional AC power adapters are required. The kit is also plug-and-play - no special software or drivers needed. Wall Plates provide a clean, finished look to your wiring installation, and allow USB peripherals such as Printers, Whiteboards, Hubs, etc., to be located where you need them. Rear mounted RJ45 jacks allow for easy plug-and-play connections between wall plates. USB 1.1 Compliant.

Tripp Lite highly recommends Solid Conductor Cat5e or Cat6 cable for maximum signal strength and attenuation. Tripp Lite offers pre-made, Solid Conductor, Cat6 patch cables, designed especially for our USB and Video over Cat5/6 products.

Features

- Locate USB peripherals up to 150 feet away from your computer
- Provides a finished look
- Uses readily available Cat5/Cat6 cable
- Bus Powered - no additional AC adapters required, No drivers required
- 100% Compatible with USB Hubs and other devices
- Fully compliant with USB 1.1 Specifications - Supports any Full-speed or Low-speed USB device

Specifications

OVERVIEW	
UPC Code	037332159984
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB B (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	2.20 x 8.40 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 21.34 x 16.51
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.