



Powering Business Worldwide

BP24V33 - External Battery Pack for UPS System

MODEL NUMBER: BP24V33



Highlights

- Extends runtime of Tripp Lite UPS Systems with 24V DC external battery connection
- Provides daisy-chain capability
- Simple installation; stackable
- 2 year warranty

Package Includes

- BP24V33 external battery pack
- Warranty information
- Instruction manual

Description

Tripp Lite's BP24V33 external battery pack offers extended battery runtime when used in conjunction with Tripp Lite SmartPro UPS systems with a 24VDC external battery connection. Stackable form factor supports configuration with up to 2 battery packs stacked with the UPS on top. Rugged all metal battery enclosure safely houses UPS batteries and includes heavy gauge cabling with pre-installed DC connectors for simple installation. Additional output connector allows multiple BP24V33 battery packs to be daisy-chained to the UPS for even longer extended run operation.

Features

- Offers extended-run UPS operation when used in conjunction with Tripp Lite UPS systems with a 24V DC external battery connection
- Supports stacking installation of two battery packs with the UPS on top
- Includes input and output connectors to support the connection of multiple battery packs for even longer extended run operation
- Includes heavy gauge cabling with high current DC connectors for simple installation
- 2 year warranty

Specifications

OVERVIEW	
UPC Code	037332080400
BATTERY	
Expandable Runtime	Yes
Expandable Runtime Description	Red female DC connector for additional battery packs
DC System Voltage (VDC)	24
UPS Connection	3 ft. attached cable with red DC connector
Typical Battery Lifespan	4-6 years typical (North America)



Powering Business Worldwide

PHYSICAL	
Material of Construction	Steel
Form Factors Supported	Floorstanding tower format. Stackable
Shipping Dimensions (hwd / in.)	14.50 x 13.50 x 19.25
Shipping Dimensions (hwd / cm)	36.83 x 34.29 x 48.90
Shipping Weight (lbs.)	65.48
Shipping Weight (kg)	29.70
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	20.32 x 29.21 x 33.02
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.