

External UPS Battery Pack, 80 10Ah Batteries Included - S3M40KX S3MX-Series 3-Phase UPS System

MODEL NUMBER: BP480V10



Backup battery pack provides extended runtime for compatible Tripp Lite S3MX-Series 3-phase UPS systems.

Description

Tripp Lite's BP480V10 External Battery Cabinet offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Includes internal disconnect for battery isolation. Compatible UPS Systems: S3M40KX only.

Features

+/-240VDC Backup Battery Pack Gives Your Compatible UPS System Extended RuntimeThe BP480V10 is compatible only with Tripp Lite's 3-phase S3M40KX that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained to as many as seven external battery packs for even longer extended-run operation. The UPS battery pack consists of a steel battery cabinet and 80 sealed 10Ah lead acid batteries. Hardwire installation is safe and simple. Circuit breakers provide overcurrent protection. Internal disconnect for battery isolation is included.

One-Year WarrantyThe BP480V10 is backed by a one-year warranty, ensuring reliability and performance.

Highlights

- Extends runtime of compatible UPS systems using special +/- 240VDC configuration
- Black steel cabinet matches UPS systems to give your server room a consistent look
- Requires hardwire installation; circuit breakers provide overcurrent protection
- Multiple battery pack cabinets may be connected in parallel to increase runtime

Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain as many as 7 battery packs to provide even longer extended-run operation for backing up essential equipment in your server room or data center

System Requirements

- Tripp Lite S3M40KX or other UPS system specifying compatibility with this external battery pack

Package Includes

- BP480V10 External Battery Pack for S3M40KX UPS System - 80 10Ah Batteries Included
- Cable for jack, 32 in. (81.3 cm), 1/0 AWG
- Attachment hardware for battery cable



- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332231055
INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime
DC System Voltage (VDC)	+/- 240VDC
UPS Connection	Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations)
Typical Battery Lifespan	10 year design lifespan
Expandable Runtime	Yes
PHYSICAL	
External Battery Pack Form Factor	Tower
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	101.85 x 38.00 x 91.95
Shipping Dimensions (hwd / in.)	40.10 x 14.96 x 36.20
Shipping Weight (kg)	290.00
Shipping Weight (lbs.)	639.34
Unit Dimensions (hwd / cm)	83,57 x 25,02 x 77,98
Unit Dimensions (hwd / in.)	32.9 x 9.85 x 30.7
Unit Weight (kg)	273.00
Unit Weight (lbs.)	601.87
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty