

External UPS Battery Pack, 40 65Ah, No Batteries Included - Compatible S3MX-Series 3-Phase UPS System

MODEL NUMBER: BP480V65-NIB



Includes internal battery wiring and accessories for 40 user-supplied 65Ah batteries to extend runtime of a compatible UPS.

Features

+/-240VDC Backup Battery Pack — You Provide the Batteries The BP480V65-NIB is compatible only with Tripp Lite's 3-phase S3M30KX-NIB, S3M40KX-NIB, S3M60KX, S3M80KX, S3M100KX, S3M120KX, S3M160KX, S3M200KX and other UPS systems that specify the use of this battery pack. The UPS battery pack includes the steel enclosure and all required internal wiring and accessories for a quantity of 40 user-supplied 65Ah internal batteries (batteries not included). For the same battery pack with internal batteries included, see Tripp Lite's BP480V65.

Daisy-Chain Multiple Cabinets for Even Longer Extended-Run Operation Multiple battery pack cabinets may be connected in parallel to provide the 3-phase UPS system with more runtime. Up to three external battery packs may be connected to the S3M30KX-NIB, S3M40KX-NIB, S3M60KX and S3M80KX. The S3M100KX, S3M120KX, S3M160KX and S3M200KX units can handle as many as seven BP480V65-NIBs connected in parallel. Hardwire installation is safe and simple. Circuit breakers provide overcurrent protection. Internal disconnect for battery isolation is included.

One-Year Warranty The BP480V65-NIB is backed by a one-year warranty, ensuring reliability and performance.

Highlights

- Extends runtime of compatible UPS systems using special +/- 240VDC configuration
- Requires 40 user-supplied 65Ah sealed lead acid batteries for operation
- The battery cabling on this cabinet is designed for batteries that have "threaded battery posts" as described on the battery cabinet owner's manual.
- Black steel cabinet matches UPS systems to give your server room a consistent look
- Requires hardwire installation; circuit breakers provide overcurrent protection
- Multiple battery pack cabinets may be connected in parallel to increase runtime

Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain to multiple additional battery packs to provide even longer extended-run operation for backing up essential equipment in your data center or server room

System Requirements

- The BP480V65-NIB is compatible with Tripp Lite S3M30KX-NIB, S3M40KX-NIB, S3M60KX, S3M80KX, S3M100KX, S3M120KX, S3M160KX, and S3M200KX.
- 40 user-supplied 65Ah sealed lead acid batteries

Package Includes

- BP480V65-NIB External Battery Pack - Batteries Not Included
- Cable for jack, 32 in. (81.3 cm), 1/0 AWG
- Attachment hardware for battery cable
- Owner's manual

Specifications

| OVERVIEW | |
|---|--|
| UPC Code | 037332231109 |
| INPUT | |
| Input Phase | 3-Phase |
| BATTERY | |
| Expandable Runtime | Yes |
| DC System Voltage (VDC) | +/- 240VDC |
| UPS Connection | Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations) |
| Typical Battery Lifespan | 10 year design lifespan |
| PHYSICAL | |
| Material of Construction | Steel |
| External Battery Pack Form Factor | Tower |
| Installation Form Factors Supported with Included Accessories | Tower |
| Shipping Dimensions (hwd / in.) | 66.14 x 37.00 x 52.76 |
| Shipping Dimensions (hwd / cm) | 168.00 x 93.98 x 134.01 |
| Shipping Weight (lbs.) | 470.91 |
| Shipping Weight (kg) | 213.60 |
| Unit Dimensions (hwd / in.) | 59.050 x 32.520 x 44.680 |
| Unit Dimensions (hwd / cm) | 149 x 82,6 x 113,49 |
| Unit Weight (lbs.) | 347.45 |
| Unit Weight (kg) | 157.60 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |