

48V Extended Battery Module (EBM) for SU1500XLCD SmartOnline UPS System, Tower

MODEL NUMBER: BP48V



Provides extended runtime for compatible UPS systems in education, healthcare, military, government and other IT applications in small or mid-size networks.

Features

Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The valve-regulated lead-acid (VRLA) BP48V offers extended battery runtime when used in conjunction with the SU1500XLCD SmartOnline® UPS system. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Highlights

- Connects to select expandable SmartOnline UPS systems to add critical runtime
- Includes heavy-gauge battery cabling with high-current 48V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime

System Requirements

Compatible only with 2023 redesign SU1500XLCD UPS systems

Package Includes

- 48V Extended Battery Module
- External battery cable
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332279743
INPUT	
Input Phase	Single-Phase
Input Cord Details	15.7 in. connector cord
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	48
UPS Connection	UPS specific DC connector
PHYSICAL	
Primary Form Factor	Tower



Powering Business Worldwide

TRIPP LITE
SERIES

Rack Height	0U
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	14.85 x 11.66 x 22.45
Shipping Weight (kg)	26.31
Unit Dimensions (hwd / in.)	9.930 x 6.300 x 17.090
Unit Weight (lbs.)	54.02
Unit Weight (kg)	24.50
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Extended Service Plans	ADVANCED DEPOT EXCHANGE Service Part Number: TL9SW5Y-3000BCParts, electronics and batteries coverageNext business day shippingTechnical support 5-YEAR ON-SITE PLAN (US ONLY) Service Part Number: TLWEBN75XX-7000BCOnsite parts and labor coverage for 5 yearsParts, electronics and batteries coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical support

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.