

48V Extended Battery Module (EBM) for Select 1500VA SmartPro UPS Systems, 2U Rack/Tower, TAA

MODEL NUMBER: **BP48VRXLTA**



External battery pack provides extended runtime for compatible UPS systems in government, military, education, retail, financial or healthcare applications.

Features

Backup Battery Module Gives Your Compatible UPS System Extended RuntimeThe BP48VRXLTA offers extended battery runtime when used in conjunction with certain Eaton Tripp Lite series 1500VA SmartPro® UPS systems, such as the SMART1500RXLTA. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.**Equipped with External Battery Auto-Detect**The automatic battery detection feature works with the connected UPS system to detect the EBM and automatically update runtimes. Up to four EBMs can be daisy-chained to a single UPS.**Versatile Design Supports 2U Rack or Tower Installation**This VRLA battery pack's multi-use form factor supports mounting in 2U of space in EIA-standard 19-inch open frame racks or enclosures using the included 4-post rail kit and mounting brackets. Tower stands are also included for optional upright configuration.**TAA-Compliant for GSA Schedule Purchases**The BP48VRXLTA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Connects to SMART1500RXLTA UPS to provide additional battery runtime
- Auto-detect feature lets compatible UPS systems automatically update runtime
- Versatile design allows for 2U rack mounting or upright tower configuration
- Daisy-chain connector supports additional battery packs for even longer runtime
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Compatible only with Eaton Tripp Lite series SMART1500RXLTA SmartPro UPS system

Package Includes

- BP48VRXLTA 48V Extended Battery Module
- External battery cable
- Auto-detection cable
- Rack-mounting hardware
- Tower support stands
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	786689816032
INPUT	
Input Phase	Single-Phase
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	48



Powering Business Worldwide

TRIPP LITE
SERIES

Internal UPS Replacement Battery Cartridge	 744-A3297 </td>
Battery Replacement Description	Hot-swappable, user-replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
UPS Connection	Detachable power and data cables with series specific connectors.
Typical Battery Lifespan	3 to 5 Years
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower
Minimum Required Rack Depth (cm)	48.26
Minimum Required Rack Depth (inches)	19
Unit Dimensions (hwd / in.)	3.400 x 17.200 x 17.600
Unit Weight (lbs.)	61.8
Unit Weight (kg)	28.03
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cTUVus; cUL Listed
Product Compliance	CE (Europe); RoHS; Trade Agreements Act (TAA); WEEE
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year warranty, 3 year with registration. Note: Registration is required </td>

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.