

72V Extended Battery Module (EBM) for Select 2200VA and 3000VA SmartPro UPS Systems, 2U Rack/Tower, TAA

MODEL NUMBER: **BP72VRXLTA**



External battery pack provides extended runtime for compatible UPS systems in government, military, education, retail, financial or healthcare applications.

Features

Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The BP72VRXLTA offers extended battery runtime when used in conjunction with certain Eaton Tripp Lite series 2200VA and 3000VA SmartPro® UPS systems, such as the SMART2200RXLTA and SMART3000RXLTA. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Equipped with External Battery Auto-Detect

The automatic battery detection feature works with the connected UPS system to detect the EBM and automatically update runtimes.

Versatile Design Supports 2U Rack or Tower Installation

This VRLA battery pack's multi-use form factor supports mounting in 2U of space in EIA-standard 19-inch open frame racks or enclosures using the included 4-post rail kit and mounting brackets. Tower stands are also included for optional upright configuration.

TAA-Compliant for GSA Schedule Purchases

The BP72VRXLTA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	786689816049
INPUT	
Input Phase	Single-Phase

Highlights

- Connects to SMART2200RXLTA and SMART3000RXLTA UPS systems to provide additional runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Auto-detect feature lets compatible UPS systems automatically update runtime
- Versatile design allows for 2U rack mounting or upright tower configuration
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Compatible only with Eaton Tripp Lite series SMART2200RXLTA and SMART3000RXLTA SmartPro UPS systems

Package Includes

- BP72VRXLTA 72V Extended Battery Module
- External battery cable
- Auto-detection cable
- Rack-mounting hardware
- Tower support stands
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	72
Internal UPS Replacement Battery Cartridge	 744-A3121
Battery Replacement Description	Hot-swappable, user-replaceable batteries. EBM requires 2x 744-A3121 Replacement Battery Cartridges.
UPS Connection	Detachable power and data cables with series specific connectors.
Typical Battery Lifespan	3 to 5 Years
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower
Minimum Required Rack Depth (cm)	63.50
Minimum Required Rack Depth (inches)	25
Unit Dimensions (hwd / in.)	3.400 x 17.200 x 23.700
Unit Weight (lbs.)	89.1
Unit Weight (kg)	40.42
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA C22.2; cTUVus
Product Compliance	CE (Europe); RoHS; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.