

External 72V 2U Rackmount Battery Pack for select Tripp Lite UPS Systems (BP72V15-2U)

MODEL NUMBER: **BP72V15-2U**



Highlights

- Extends the runtime of compatible 72V Tripp Lite UPS Systems
- Supports 2U rackmount installation, 4 post installation accessories included
- Options for 2 post rackmount and wallmount installation available

Package Includes

- BP72V15-2U external battery pack with attached DC cabling
- 4 post compatible rack mounting hardware
- Owner's manual

Description

BP72V15-2U rackmount external battery pack offers extended battery runtime when used in conjunction with expandable 72V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2 post center-mounting and wall mount installation available.

Compatible with these UPS Systems - SU3000RTXL2U, SU3000RTXL3U, SU3000RTXLCD2U, SU3000RTXLCD3U, SU3000RTXR3U, SU3000RTXR3UHW, SU3000XL, SU3000XLCD, SUIINT3000RTXL2U, SUIINT3000RTXL3U, SU3000LCD2UHV, SUIINT3000LCD2U and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 72V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- 2POSTRMKITWM option supports balanced 2 point center-mounting in 2 post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- NOTE: LIMIT OF 1 BP72V15-2U PER UPS, SEE BP72V18-2US or BP72V28RT-3U FOR MULTI-PACK COMPATIBILITY

Specifications

OVERVIEW	
UPC Code	037332124333
INPUT	
Input Phase	Single-Phase

BATTERY	
DC System Voltage (VDC)	72
UPS Connection	Attached cable with black 3-point DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;2POSTRMKITWM&nbsp;); Wallmount (&nbsp;2POSTRMKITWM&nbsp;);
Minimum Required Rack Depth (cm)	67.94
Minimum Required Rack Depth (inches)	26.75
Shipping Dimensions (hwd / in.)	10.00 x 26.00 x 28.00
Shipping Dimensions (hwd / cm)	25.40 x 66.04 x 71.12
Shipping Weight (lbs.)	120.00
Shipping Weight (kg)	54.43
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 20.750
Unit Dimensions (hwd / cm)	8.9 x 52.7 x 52.7
Unit Weight (lbs.)	72.4
Unit Weight (kg)	32.84
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.