

## Multi-Device Charging Station, 32 AC Outlets, iPad and Android Tablets, Wall-Mount and Cart Options, Black

MODEL NUMBER: CS32AC



### Highlights

- AC charging and storage for 32 iPad and Android tablets
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Mounts to wall, desk, table or floor and supports cart option
- 10-ft. (3.05 m) power cord and built-in AC outlets for each device

### Package Includes

- CS32AC 32-Device AC Charging Station Cabinet
- (2) Keys for door lock
- Owner's manual

Locking steel cabinet provides AC charging, secure storage and cord management for up to 32 iPad, Android, Kindle and Surface tablets, with mobile cart option. For education, office, commercial, retail, industrial and healthcare environments.

### Features

#### Convenient Charging

- 32 AC outlets charge up to 32 iPad, Android, Kindle or Surface tablets
- Compatible with all devices that charge via user-supplied USB power adapters, including iPad, Android, Kindle, Kindle Fire and Surface tablets and iPhone, Android and Windows smartphones
- 10-ft. (3.05 m) AC input cord reaches distant outlets

#### Comprehensive Protection

- Sturdy steel construction and powder-coated finish provide long-term durability
- Door locks with included keys to prevent device theft, damage or tampering
- Flow-through ventilation prevents devices from overheating
- Coated shelves shield devices from scratches and scuffs
- Built-in circuit breakers protect against overloads

#### Clutter-Free Organization

- AC outlets, device AC adapters and cords store out of sight
- Shelves include charging cord access ports for each device
- Toolless trim panels permit quick access to AC adapters and cords
- Outlets spaced to fit bulky power adapters without blocking adjacent outlets

#### Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor

- Converts to mobile cart with optional CSHANDLEKIT accessory
- Door opens 180 degrees and side panels are removable for clear access
- Removable dividers accommodate thicker devices like battery chargers

## Specifications

OVERVIEW	
UPC Code	037332185242
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Charger Functions	Charge; Secure
Device Compatibility	Tablet; Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	32
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 12A
Overcharge Protection	No
Charging Amps per Port	12A
PHYSICAL	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	41.00 x 26.00 x 28.80
Shipping Dimensions (hwd / cm)	104.14 x 66.04 x 73.15
Shipping Weight (lbs.)	182.00



Powering Business Worldwide



Shipping Weight (kg)	82.55
Slot Dimensions - Bottom (hwd / in.)	9.7 x 0.8 x 13.9
Slot Dimensions - Bottom (hwd / mm)	247 x 20.1 x 353.8
Slot Dimensions - Top (hwd / in.)	9.9 x 0.8 x 13.9
Slot Dimensions - Top (hwd / mm)	251 x 20.1 x 353.8
Unit Dimensions (hwd / in.)	35.600 x 23.600 x 21.600
Unit Dimensions (hwd / cm)	90.42 x 59.9 x 54.86
Unit Weight (lbs.)	96
Unit Weight (kg)	43.54
Number of Shelves	2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.