


Important Note

Includes conversion kit assembly only. CSC36AC charging station cart and monitor sold separately.

Display Mount Adapter Kit for 36-Device AC Charging Station Cart

MODEL NUMBER: CSC36DM



Allows a flat-panel television or monitor to be mounted to your Tripp Lite CSC36AC charging station cart (sold separately), converting it to a mobile display cart. Recommended for environments that use mobile devices daily.

Description

The CSC36DM Display Mount Adapter Kit includes all installation and mounting hardware needed to attach a flat-panel television or monitor to your CSC36AC 36-Device AC Charging Station Cart. Recommended for schools, offices, warehouses, healthcare facilities and other environments in which tablets, laptops or Chromebooks are used on a daily basis, the CSC36DM fits most flat- or recessed-back displays up to 60 inches.

A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles. Adjusting the tilt angle is simple using the easy-grip twin knobs located on the adapter brackets. The durable all-metal unit with scratch-resistant powder-coated finish supports up to 100 pounds (45.4 kilograms).

The CSC36DM is designed to fit through standard doorways when assembled. It conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm and 800 x 400 mm.

Features

Mounts Your TV or Monitor to Your CSC36AC Charging Station Cart

- Fits most flat-panel televisions or monitors up to 60 in.
- Ideal for schools, offices, warehouses, healthcare facilities and other environments in which tablets, laptops or Chromebooks are used every day
- All installation and mounting hardware included

Convenient Angle Adjustment

- -10° to 10° tilt capability provides comfortable viewing from multiple angles
- Improves viewing angles in applications where audience is below the display
- Easy-grip knobs allow simple adjustment of tilt angle

Highlights

- Fits most flat- or recessed-back displays up to 60 in.
- -10° to 10° tilt capability for comfortable viewing
- Includes all necessary installation and mounting hardware
- Easily rolls through standard doorways when assembled
- Supports up to 100 lbs (45.4 kgs)

Package Includes

- Display plate
- (2) Adapter brackets
- (2) Outrigger tubes
- (2) Upright supports
- (24) M8 x 16 screws
- (8) M6 x 15 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- Installation guide



Powering Business Worldwide



Durable Metal Construction

- Supports up to 100 lbs (45.4 kgs)
- Scratch-resistant powder-coated finish
- Easily rolls through standard doorways when assembled

VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm and 800 x 400 mm

Specifications

OVERVIEW	
UPC Code	037332204035
Accessory Type	Displaymount Adapter Kit
Accessory Class	Charging Station Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	11.00 x 13.19 x 68.89
Shipping Dimensions (hwd / cm)	27.94 x 33.50 x 174.98
Shipping Weight (lbs.)	99.66
Shipping Weight (kg)	45.21
Unit Dimensions (hwd / in.)	57.500 x 29.500 x 42.000
Unit Dimensions (hwd / cm)	146.05 x 74.93 x 106.68
Unit Weight (lbs.)	92.84
Unit Weight (kg)	42.11
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.