

Mobile Cart Conversion Kit with Handle, Casters and Power Cord Manager for 16-Device AC and USB Charging Stations

MODEL NUMBER: CSHANDLEKIT2



Adds a reversible handle, rolling casters and a power cord manager to your CSC16AC, CSC16ACW, or CSC16USB charging station. Ideal for schools, offices and other locations where tablets, laptops or Chromebooks are used.

Description

The CSHANDLEKIT2 Mobile Cart Conversion Kit includes a reversible handle, rolling casters and a power cord manager that easily attach to your Tripp Lite 16-device AC or USB charging station, such as CSC16AC, CSC16ACW and CSC16USB. Perfect for schools, offices, warehouses, healthcare facilities and other locations where multiple tablets, laptops or Chromebooks are used regularly, the CSHANDLEKIT2 allows for smooth mobility of your charging station. The four rolling casters are non-marking for environments where this is mandatory. All four casters lock into place for maximum stability at rest. The casters, easy-grip handle and convenient power cord manager mount to the charging station using the included hardware. The CSHANDLEKIT2 supports a maximum load capacity of 350 pounds.

Features

Converts Your 16-Device AC or USB Charging Station Into a Mobile Cart

- Adds reversible handle, rolling casters and power cord manager to CSC16AC, CSC16ACW, CSC16USB and other compatible charging stations
- Ideal for schools, offices, warehouses, healthcare facilities and other locations where multiple tablets, laptops or Chromebooks are used regularly
- Supports a maximum load capacity of 350 lb.
- 4 swivel/locking casters—all are non-marking
- Comes with all necessary installation hardware

Specifications

Highlights

- Converts a 16-device charging station into a mobile cart
- Supports maximum load capacity of 350 lb.
- Includes reversible handle and power cord manager
- Includes 4 swivel/locking casters
- Comes with all necessary installation hardware

Package Includes

- Reversible handle
- Power cord manager
- (4) Non-marking casters, 4 in.
- (2) Caster-mounting brackets
- (2) Handle-mounting brackets
- (12) M5 screws
- (12) M5 locking washers
- (16) M6 screws
- (16) M6 locking washers
- (16) M6 flat washers
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332196385
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	11.18 x 47.24 x 53.34
Shipping Dimensions (hwd / in.)	4.40 x 18.60 x 21.00
Shipping Weight (kg)	8.57
Shipping Weight (lbs.)	18.90
Unit Weight (kg)	9.59
Unit Weight (lbs.)	21.15
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>