

Mobile Cart Conversion Kit with Handle, Casters and Power Cord Manager for Tablet/Chromebook Charging Stations

MODEL NUMBER: CSHANDLEKIT



Adds a reversible handle, rolling caster wheels and a power cord manager to select AC and USB tablet/Chromebook charging stations. Ideal for schools, offices and other locations where multiple tablets or Chromebooks are used.

Description

The CSHANDLEKIT Mobile Cart Conversion Kit includes a reversible handle, rolling caster wheels and power cord manager that easily attach to your AC or USB charging station.* Perfect for schools, offices, warehouses, healthcare facilities and other locations where multiple tablets or Chromebooks are used regularly, the CSHANDLEKIT allows for smooth mobility of your charging station. The four rolling casters are non-marking for environments where this is mandatory, and two of the casters lock into place for maximum stability at rest. The casters, easy-grip handle and convenient power cord manager mount to the charging station using the included hardware. The CSHANDLEKIT supports a maximum load capacity of 350 pounds.

*CS16USB charging stations excluded

Features

Converts Your AC or USB Tablet/Chromebook Charging Station Into a Mobile Cart*

- Adds reversible handle, rolling caster wheels and power cord manager to your charging station
- Ideal for schools, offices, warehouses, healthcare facilities and other locations where multiple tablets or Chromebooks are used regularly
- Supports a maximum load capacity of 350 lb.
- 2 swivel/locking casters and 2 swivel-only casters—all are non-marking
- Comes with all necessary installation hardware

Highlights

- Converts an AC or USB charging station into a mobile cart*
- Supports maximum load capacity of 350 lb.
- Includes reversible handle and power cord manager
- Includes 2 swivel/locking casters and 2 swivel-only casters
- Comes with all necessary installation hardware

Package Includes

- Reversible handle
- Power cord manager
- (4) Non-marking casters, 4 in.
- (2) Caster-mounting brackets
- (2) Handle-mounting brackets
- (12) M5 screws
- (12) M5 locking washers
- (16) M6 screws
- (16) M6 locking washers
- (16) M6 flat washers
- Owner's Manual



Specifications

OVERVIEW	
UPC Code	037332188939
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	11.68 x 70.00 x 27.99
Shipping Dimensions (hwd / in.)	4.60 x 27.56 x 11.02
Shipping Weight (kg)	10.43
Shipping Weight (lbs.)	23.00
Unit Weight (kg)	9.59
Unit Weight (lbs.)	21.15
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>