



Powering Business Worldwide

Network Surge Suppressor - Essential protection for TV/VCR coaxial lines

MODEL NUMBER: DCATV



Highlights

- Complete dataline (F coaxial) surge protection
- Protects against the effects of electrostatic discharge
- Lifetime product warranty
- Heavy duty grounding lead

Description

Tripp Lite's DCATV offers type F coax line surge suppression for satellite receivers and broadcast antennas. Convenient coax input and output connections accept standard type F coax wiring. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges. Tripp Lite network surge suppressors reduce blown interface connections by safely shunting dataline surges to ground. Six inch heavy gauge grounding lead connects to designated grounding lugs. Lifetime warranty. **Not for use with cable modems.**
 SUPPRESSION: 1 set type F coax jacks, protects center and shield, 7.5V clamping

Features

- DCATV offers type F coax line surge suppression satellite receivers and broadcast antennas. **Not for use with cable modems.**
- Type F coax input and output connections
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground
- 6 inch heavy gauge grounding lead connects to designated grounding lugs on protected equipment
- Lifetime product warranty

Specifications

| OVERVIEW | |
|--------------------------------|--------------|
| UPC Code | 037332010889 |
| INPUT | |
| Recommended Electrical Service | 120V, 230V |
| Input Plug Type | F-Type Coax |
| Input Cord Length (ft.) | 0 |
| Right-Angle Plug | No |



Powering Business Worldwide

| | |
|--|---------------------------|
| Input Cord Length (m) | 0.00 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Output Receptacles | Network |
| Circuit Breaker (amps) | 750 |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | No |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 0 |
| Automatic Shut-Off | No |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | Yes |
| Network (Ethernet) Protection | No |
| Additional Dataline Protection | Center & Shield |
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Housing Color | White |
| Mounting Holes or Slots | No |
| Shipping Dimensions (hwd / in.) | 9.20 x 4.25 x 10.20 |
| Shipping Dimensions (hwd / cm) | 23.37 x 10.80 x 25.91 |
| Shipping Weight (lbs.) | 1.76 |
| Shipping Weight (kg) | 0.80 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 3.000 |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.