

Triple-Display Flex-Arm Desktop Clamp for 17” to 30” Flat-Screen Displays - USB and Audio Ports, Aluminum

MODEL NUMBER: DDR1730TAL



Aluminum desk clamp mounts your 17 to 30 in. monitors at a comfortable height to free up valuable space on your desk or work area.

Features

Rugged Aluminum Desk Clamp Lifts Your Monitors Above Your Work Area’s Surface

This VESA-compliant desktop clamp mounts three flat-screen displays above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1730TAL fits most flat-panel monitors from 17 to 30 inches. The durable aluminum frame tolerates frequent adjustments, and the two swiveling aluminum arms support up to 15.4 pounds apiece. Instead of clamping the unit to your desktop, you may install it using the included grommet. All hardware is included. Cable management brackets along the arms prevent excess cord clutter.

Swivel, Tilt and Rotate the Screens to Find the Most Comfortable Viewing Angles

The flex arms adjust independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -90° to +90° tilt, -90° to +90° swivel and 90° rotation for positioning your screens. Easy screen adjustment lets you quickly find just the right angles without interrupting your workday.

Connect Your Favorite Devices to Help You Get Through the Workday

The base of the DDR1730TAL features a USB 3.0 port for connecting a smartphone or other USB device. Two 3.5 mm audio jacks allow connection of a microphone and speakers.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

Highlights

- Sturdy aluminum frame clamps securely to your desk for mounting displays
- -90° to +90° tilt, -90° to +90° swivel and 90° rotation help you find the perfect angle
- Base includes a USB 3.0 port and dual 3.5 mm audio ports for connecting peripherals
- Durable aluminum flex arms blend into any décor and support up to 15.4 lb. each
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

Applications

- Lift 3 monitors above your standing desk or workstation to free up valuable surface space
- Swivel, tilt and/or rotate your screens for the most comfortable viewing angle

System Requirements

Flat-screen monitors from 17 to 30 in.

Package Includes

- DDR1730TAL Triple-Display Flex-Arm Desktop Clamp
- Mounting hardware
- Owner’s manual

Specifications

OVERVIEW	
UPC Code	037332262516



Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
VESA Pattern (mm)	75x75; 100x100
Degrees of Motion	-90/+90 for Tilt, Swivel and Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	76.2
Maximum Screen Size (in.)	30
Maximum Weight Capacity (kg)	7
Maximum Weight Capacity (lbs.)	15.4
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.2
Motion	Full
Mounting Location	Desk Clamp; Grommet
Number of Displays	3
Unit Dimensions (hwd / cm)	73.91 x 151.89 x 19.30
Unit Dimensions (hwd / in.)	29 x 59.8 x 7.6
Unit Weight (kg)	9.39
Unit Weight (lbs.)	20.7
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	Yes
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>