

# Dual-Monitor Flex-Arm Desktop Clamp for 13" to 27" Displays

MODEL NUMBER: DDR1327SDFC-1



Desk clamp mounts your 13 to 27 in. monitors at a comfortable height to free up valuable space on your desk or work area.

## Features

### Rugged Steel Desk Clamp Lifts Your Monitors Above Your Work Area's Surface

This VESA-compliant desktop clamp mounts two flat-screen displays above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1327SDFC-1 fits most flat-panel monitors from 13 to 27 inches. The clamp fits desktops ranging in thickness from 0.4 to 3.3 inches (10 to 85 millimeters). All hardware is included. Cable management brackets along the arms prevent excess cord clutter.

### Swivel, Tilt and Rotate the Screens to Find the Most Comfortable Viewing Angles

The durable steel frame stands up to frequent adjustments, and the two flex arms support up to 17.6 pounds (8 kilograms) apiece. The flex arms adjust independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the DDR1327SDFC-1 features -30° to +30° tilt, -90° to +90° swivel and 360° rotation for positioning your screens.

### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

## Specifications

OVERVIEW	
UPC Code	037332266118
Device Compatibility	Monitor/HDTV
PHYSICAL	

## Highlights

- Steel frame clamps securely to your desk for mounting displays at comfortable levels
- -30° to +30° tilt, -90° to +90° swivel and 360° rotation help you find the perfect angle
- Dual flex arms adjust independently and support displays up to 17.6 lb. each
- Cable management brackets keep cords organized and help prevent excess clutter
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

## Package Includes

- DDR1327SDFC-1 Dual-Display Flex-Arm Desktop Clamp
- Mounting hardware
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Material of Construction	Steel
Color	Black
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-30/+30 Tilt; 180 Swivel; 360 VESA head Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	17.6
Maximum Weight Capacity (kg)	8
Number of Displays	2
Unit Dimensions (hwd / in.)	19.6 x 34.9 x 4.9
Unit Dimensions (hwd / cm)	49.78 x 88.65 x 12.45
Unit Weight (lbs.)	8.3
Unit Weight (kg)	3.76
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS3, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>