

# Single-Display Flex-Arm Desktop Clamp for 13” to 34” Displays - USB and Audio Ports, Aluminum

MODEL NUMBER: DDR1732SAL



Aluminum desk clamp mounts your 13 to 34 in. monitor at a comfortable height to free up valuable space on your desk or work area.

## Features

### Rugged Aluminum Desk Clamp Lifts Your Monitor Above Your Work Area’s Surface

This VESA-compliant desktop clamp mounts a flat- or curved-screen display above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1732SAL fits most flat- and curved-panel monitors from 13 to 34 inches. The durable aluminum frame tolerates frequent adjustments, and the swiveling aluminum arm supports up to 19.8 pounds (9 kg). Instead of clamping the unit to your desktop, you may install it using the included grommet. All hardware is included. Cable management brackets along the arms prevent excess cord clutter.

### Swivel, Tilt and Rotate the Screens to Find the Most Comfortable Viewing Angles

The flex arm adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -90° to +90° tilt, -90° to +90° swivel and 90° rotation for positioning your screen. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday.

### Connect Your Favorite Devices to Help You Get Through the Workday

The base of the DDR1732SAL features a USB 3.0 port for connecting a smartphone or other USB device. Two 3.5 mm audio jacks allow connection of a microphone and speakers.

### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

## Highlights

- Sturdy aluminum frame clamps securely to your desk for mounting your display
- -90° to +90° tilt, -90° to +90° swivel and 90° rotation help you find the perfect angle
- Base includes a USB 3.0 port and dual 3.5 mm audio ports for connecting peripherals
- Durable aluminum flex arm blends into any décor and supports up to 19.8 lb.
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

## Applications

- Lift a monitor above your standing desk or workstation to free up valuable surface space
- Swivel, tilt and/or rotate your screen for the most comfortable viewing angle

## System Requirements

Flat- and curved-screen monitors from 13 to 34 in.

## Package Includes

- DDR1732SAL Single-Display Flex-Arm Desktop Clamp
- Mounting hardware
- Owner’s manual

## Specifications

OVERVIEW	
UPC Code	037332262493



Device Compatibility	Monitor/HDTV
<b>PHYSICAL</b>	
Color	Silver
VESA Pattern (mm)	75x75; 100x100
Degrees of Motion	-90/+90 for Tilt, Swivel and Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	86.4
Maximum Screen Size (in.)	34
Maximum Weight Capacity (kg)	9
Maximum Weight Capacity (lbs.)	19.8
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Motion	Full
Mounting Location	Desk Clamp; Grommet
Number of Displays	2
Unit Dimensions (hwd / cm)	82.4 x 62.74 x 11.43
Unit Dimensions (hwd / in.)	32.3 x 24.7 x 4.5
Unit Weight (kg)	4.63
Unit Weight (lbs.)	10.2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
<b>SPECIAL FEATURES</b>	
Cord Management	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS3, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>