

# Portable Digital Signage Stand for 49" to 70" Flat-Screen and Curved-Screen Displays

MODEL NUMBER: DMPDS4970



Easel-style portable TV stand sets up quickly for delivering your message in a classroom, lobby or anywhere else with heavy foot traffic.

## Features

### Set Up Your Digital Signage Wherever Your Audience Is

This portable TV stand fits most flat-panel and curved-panel displays, whiteboards and monitors from 49 to 70 inches (124 to 178 centimeters). It's easy to assemble with secure locking collars for convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels.

### Durable Wood and Steel Frame Designed to Last

The frame withstands the stress of repeated adjustments and supports up to 88 pounds (40 kilograms). An included safety strap prevents the mounted display from tipping.

### Built-In Cable Management Helps Eliminate Clutter

Equipment cables route through clips on the stand's legs to keep them organized and out of the way. Rubber pads are included to ensure your display remains level on an uneven surface.

### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400. All hardware is included.

## Highlights

- Supports most monitors, whiteboards and interactive displays from 49 to 70 in.
- Durable wood and steel frame blends into any room décor and supports up to 88 lb.
- Easel-style stand features safety strap to prevent display from tipping
- Locks into place with one convenient snap for easy, quick assembly
- Cable management clips keep cords organized and prevent cable clutter

## Applications

- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session
- Move a display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical

## System Requirements

Flat- or curved-screen television, monitor, digital whiteboard or interactive display from 49 to 70 in.

## Package Includes

- DMPDS4970 Portable Digital Signage Stand
- Assembly hardware
- Owner's manual

## Specifications

| OVERVIEW             |              |
|----------------------|--------------|
| UPC Code             | 037332263872 |
| Device Compatibility | Monitor/HDTV |
| PHYSICAL             |              |



Powering Business Worldwide



|                                      |   |
|--------------------------------------|---|
| Color                                | Black   |
| Material of Construction             | Steel   |
| VESA Pattern (mm)                    | 200x200; 300x200; 300x300; 400x200; 400x300; 400x400; 400x600 |
| Mounting Location                    | Floor   |
| Minimum Screen Size (in.)            | 42  |
| Minimum Screen Size (cm)             | 124.5   |
| Maximum Screen Size (in.)            | 70  |
| Maximum Screen Size (cm)             | 177.8   |
| Maximum Weight Capacity (lbs.)       | 88  |
| Maximum Weight Capacity (kg)         | 40  |
| Number of Displays                   | 1   |
| Unit Dimensions (hwd / in.)          | 54.300 x 31.500 x 19.700                                      |
| Unit Dimensions (hwd / cm)           | 138 x 80 x 50   |
| Unit Weight (lbs.)                   | 88  |
| Unit Weight (kg)                     | 39.92   |
| Assembly Required                    | Yes   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| Antimicrobial                        | No  |
| Cord Management                      | Yes   |
| Tools Necessary                      | Yes   |
| <b>STANDARDS &amp; COMPLIANCE</b>    |   |
| Product Compliance                   | RoHS  |
| <b>WARRANTY &amp; SUPPORT</b>        |   |
| Product Warranty Period (Worldwide)  | 5-year limited warranty                                       |

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.