


## Portable Digital Signage Stand for 32-55 Inch Displays, Portrait or Landscape

MODEL NUMBER: DMPDS3255F



Durable steel TV stand delivers your digital signage message in either portrait or landscape mode.

### Features

#### Set Up Your Digital Signage Wherever Your Audience Is

This portable TV stand fits most flat and curved-panel displays, whiteboards and monitors from 32 to 55 inches (81 to 140 centimeters). Once assembled, it folds easily to allow convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels. The DMPDS3255F supports both portrait and landscape orientations.

#### Durable Steel Frame Designed to Last

The frame withstands the stress of repeated adjustments and supports up to 77 pounds (35 kilograms). Because the frame folds when not in use, the DMPDS3255F is easy to transport and store.

#### Built-In Cable Management Helps Eliminate Clutter

Equipment cables route through clips on the stand's legs to keep them organized and out of the way. Adjustable feet ensure your display remains level on a stable surface.

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300 and 400 x 400. Mounting hardware is included.

### Highlights

- Supports most flat and curved-panel monitors and interactive displays from 32 to 55 in.
- Durable steel frame blends into any room decor and supports up to 77 lb.
- Adjustable feet levelers provide a stable and safe foundation
- Foldable stand supports both portrait and landscape viewing
- Cable management clips keep cords organized and prevent cable clutter

### Applications

- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session
- Move a flat or curved-panel display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical
- Fold the stand and store it in a secure area when not in use

### System Requirements

Flat and curved-screen television, monitor, digital whiteboard or interactive display from 32 to 55 in.

### Package Includes

- DMPDS3255F Portable Digital Signage Stand
- Assembly hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332263858
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Material of Construction	Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400
Motion	Fixed
Mounting Location	Floor
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.82
Maximum Screen Size (in.)	55
Maximum Screen Size (cm)	139.7
Maximum Weight Capacity (lbs.)	77
Maximum Weight Capacity (kg)	35
Number of Displays	1
Unit Dimensions (hwd / in.)	14.700 x 19.900 x 50.900
Unit Dimensions (hwd / cm)	37.3 x 50.5 x 129.3
Unit Weight (lbs.)	77
Unit Weight (kg)	34.93
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.