

Portable Digital Signage Stand for 55" to 70" Flat-Screen and Curved-Screen Displays

MODEL NUMBER: DMPDS5570S



Easel-style portable TV stand sets up quickly for delivering your message in a classroom, lobby or anywhere else with heavy foot traffic.

Features

Set Up Your Digital Signage Wherever Your Audience Is

This portable TV stand fits most flat-panel and curved-panel displays, whiteboards and monitors from 55 to 70 inches (140 to 178 centimeters). It's easy to assemble with secure locking collars for convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels.

Durable Wood and Steel Frame Designed to Last

The frame withstands the stress of repeated adjustments and supports up to 88 pounds (40 kilograms). An included safety strap prevents the mounted display from tipping. A felt shelf mounts in front to hold a laptop, webcam and other essential accessories.

Built-In Cable Management Helps Eliminate Clutter

Equipment cables route through clips on the stand's legs to keep them organized and out of the way. Rubber pads are included to ensure your display remains level on an uneven surface.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400. All hardware is included.

Highlights

- Supports most monitors, whiteboards and interactive displays from 55 to 70 in.
- Rugged wood and steel frame blends into any room décor and supports up to 88 lb.
- Easel-style stand features safety strap to prevent display from tipping
- Durable felt shelf provides ample space for laptops, webcams and other accessories
- Cable management clips keep cords organized and prevent cable clutter

Applications

- Bring a digital whiteboard or interactive display into a conference room or classroom for a virtual meeting or brainstorming session
- Move a display into a lobby, hallway or trade show booth to create temporary digital signage
- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical

System Requirements

Flat- or curved-screen television, monitor, digital whiteboard or interactive display from 55 to 70 in.

Package Includes

- DMPDS5570S Portable Digital Signage Stand
- Assembly hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332263889
Device Compatibility	Monitor/HDTV



PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400; 400x600
Mounting Location	Floor
Minimum Screen Size (in.)	55
Maximum Screen Size (cm)	177.8
Maximum Screen Size (in.)	70
Minimum Screen Size (cm)	139.7
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
Number of Displays	1
Unit Dimensions (hwd / cm)	128.2 x 109 x 58.5
Unit Dimensions (hwd / in.)	50.4 x 43.2 x 23
Unit Weight (kg)	39.92
Unit Weight (lbs.)	88
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>