

Slat Rail for Slat Wall System, 40 in. (102 cm), TAA

MODEL NUMBER: DMSWSLATTAA



Adds another slat rail to increase the capacity of your existing Slat Wall System.

Features

Increases Capacity of Your Current Slat Rail

This 40-inch (102-centimeter) slat rail allows mounting of multiple displays simultaneously. It adds another slat rail to your existing Slat Rail with Posts (DMSWKITTAA, sold separately), so you can install more monitors in your workspace. Monitors are elevated above the desktop, which frees up precious workspace. You can also slide the monitors along grooves and then adjust the viewing angle for optimal ergonomics. Grooves on both sides of the slat rail accommodate independently adjustable monitor setups when desks are pushed together back-to-back.

Innovative Slat Wall System with 5 Components

The stylish aluminum DMSWSLATTAA easily installs into the DMSWKITTAA Slat Rail with Posts. In addition, this slat wall system also has options for three VESA-compliant monitor mounts (DMSW1332STAA, DMSW1332MTAA and DMSW1332LTAA), all sold separately.

TAA-Compliant for GSA Schedule Purchases

The DMSWSLATTAA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Adds a second slat rail to DMSWKITTAA Slat Rail with Posts for additional displays
- Allows customization of multiple monitors that slide into optimal viewing position
- Grooves on both sides of the slat rail benefit back-to-back workspaces
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Requires DMSWKITTAA Slat Rail with Posts
- Works with DMSW1332STAA, DMSW1332MTAA and DMSW1332LTAA monitor mounts

Package Includes

- DMSWSLATTAA Slat Rail
- (4) Screws
- Hex wrench
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332286505
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Mounting Location	Desktop



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Screen Size (in.)	32
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Shipping Dimensions (hwd / in.)	41.00 x 3.39 x 1.80
Shipping Dimensions (hwd / cm)	104.14 x 8.61 x 4.57
Shipping Weight (lbs.)	7.70
Shipping Weight (kg)	3.49
Unit Dimensions (hwd / in.)	3.500 x 39.800 x 1.300
Unit Dimensions (hwd / cm)	Monitors may be mounted to the slat wall using your choice of 3 mounts (sold separately): DMSW1332LTAA, DMSW1332MTAA or DMSW1332STAA
Unit Weight (lbs.)	5.5
Unit Weight (kg)	2.49
Mounting Details	Monitors may be mounted to the slat wall using your choice of 3 mounts (sold separately): DMSW1332LTAA, DMSW1332MTAA or DMSW1332STAA
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Height Adjustable	Yes
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.