

Slat Rail with Posts for Slat Wall System, 40 in. (102 cm), TAA

MODEL NUMBER: DMSWKITTAA



Elevates multiple monitors above your work surface to provide better viewing angles and keep desktop clean.

Features

Provides Multiple Mount Options for Your Flat-Screen TV or Monitor

This 40-inch (102-centimeter) slat rail with clamps and posts allows mounting of multiple displays simultaneously. It's ideal for workplaces, including office, hybrid and work-from-home environments. Your monitors are elevated above the desktop, which frees up precious workspace. You can also slide the monitors along grooves and then adjust the viewing angle for optimal ergonomics. Grooves on both sides of the slat rail accommodate independently adjustable monitor setups when desks are pushed together back-to-back.

Innovative Slat Wall System with 5 Components

The stylish aluminum DMSWKITTAA features side posts that clamp firmly to the edge of a flat desktop or table surface from 1.18 in. to 3.78 in. thick. In addition to the DMSWKITTAA, this slat wall system also has options for an additional slat rail for mounting more displays (DMSWSLATTAA) and three VESA-compliant monitor mounts (DMSW1332STAA, DMSW1332MTAA and DMSW1332LTAA), all sold separately.

TAA-Compliant for GSA Schedule Purchases

The DMSWKITTAA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332286468
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
Material of Construction	Aluminum

Highlights

- Allows customization of multiple monitors that slide into optimal viewing position
- Grooves on both sides of the slat rail benefit back-to-back workspaces
- Clamps securely to edge of any desktop or table from 1.18 to 3.78 in. thick
- Stylish aluminum construction blends into any decor and supports up to 33 lb.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Works with DMSW1332STAA, DMSW1332MTAA and DMSW1332LTAA monitor mounts and DMSWSLATTAA slat rail

Package Includes

- DMSWKITTAA Slat Rail with Posts
- (4) Screws
- Hex wrench
- Owner's Manual



Powering Business Worldwide

TRIPP LITE
SERIES

Mounting Location	Desktop
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Shipping Dimensions (hwd / in.)	41.30 x 6.20 x 6.30
Shipping Dimensions (hwd / cm)	104.90 x 15.75 x 16.00
Shipping Weight (lbs.)	21.50
Shipping Weight (kg)	9.75
Unit Dimensions (hwd / in.)	17.700 x 4.350 x 3.470
Unit Dimensions (hwd / cm)	44.6 x 110.1 x 81
Unit Weight (lbs.)	18.1
Unit Weight (kg)	8.21
Mounting Details	Monitors may be mounted to the slat wall using your choice of 3 mounts (sold separately): DMSW1332LTAA, DMSW1332MTAA or DMSW1332STAA
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Height Adjustable	Yes
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.