


## Swivel/Tilt Corner Wall Mount for 37" to 70" TVs and Monitors - Flat/Curved

MODEL NUMBER: **DMWC3770M**



Wall mount with split wall plates supports installation of a flat-panel or curved-screen television or monitor in a corner.

### Features

#### Corner Mount Your Flat-Panel or Curved-Screen TV or Monitor

Split wall plates allow the DMWC3770M to mount on both walls of a corner, providing a wide viewing angle in home theaters, classrooms, boardrooms, hotels, bars and restaurants. It's also a great display solution for rooms with limited wall space due to window placement or furniture arrangements. This true corner mount accommodates most flat-panel or curved-screen televisions or monitors from 37 to 70 inches. Maximum weight supported is 99 lb.

#### Adjust the Display Angle for Comfortable Viewing

One-touch adjustment capability makes it easy to optimize viewing angles. For maximum screen visibility, the articulating arms can swivel 90° left or right. The -8° to +5° tilt and -5° to +5° screen level adjustment help minimize glare and improve the audience's viewing experience.

#### Rely on Durable All-Metal Construction with Convenient Cable Access

Made of steel with a black powder-coated finish, this full-motion wall mount withstands the stress of repeated adjustments and use in public areas. An open frame design supports easy access to cables.

#### VESA Compliance Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards, such as universal mounting hole patterns, for TVs and monitors. For hassle-free display compatibility, this corner wall mount supports the following VESA mounting hole patterns: 100 x 100, 200 x 100, 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400. Mounting hardware is included.

### Highlights

- Accommodates most flat or curved screens from 37 to 70 in.
- Split wall plates mount on the adjacent walls of a corner
- One-touch adjustment makes it easy to change the viewing angle
- 90° swivel, -8° to +5° tilt and -5° to +5° screen adjustment maximize viewing comfort
- Supports displays up to 99 lb.

### Applications

- Provide flexible viewing options for seating areas in home theaters
- Take advantage of unused wall space in a classroom or conference room
- Optimize viewing for more patrons in a bar or restaurant
- Mount displays in a hotel lobby without interfering with wall art

### Package Includes

- DMWC3770M corner wall mount
- Mounting fasteners
- Wrench
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	100373322405
PHYSICAL	
Color	Black



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Degrees of Motion	90 Swivel -8/+5 Level Adjustment
Material of Construction	Steel
Maximum Screen Size (in.)	70
Maximum Weight Capacity (kg)	45
Maximum Weight Capacity (lbs.)	99
Min/Max Arm Extension (cm)	Hasta 62 cm [24.4"] de la pared
Min/Max Arm Extension (in.)	4.92 min to 20.27 max
Minimum Screen Size (in.)	37
Motion	Full
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	79.25 x 32.26 x 8.38
Shipping Dimensions (hwd / in.)	31.20 x 12.70 x 3.30
Shipping Weight (kg)	7.62
Shipping Weight (lbs.)	16.80
Unit Dimensions (hwd / cm)	61.98 x 64.26 x 41.91
Unit Dimensions (hwd / in.)	24.4 x 25.3 x 16.5
Unit Weight (kg)	6.30
Unit Weight (lbs.)	13.9
VESA Pattern (mm)	100x100; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>