

## Secure Tablet Mount Floor Stand, Height-Adjustable, Black/Silver

MODEL NUMBER: DMTBS911



Locking tablet stand recommended for displaying temporary or permanent messaging at trade shows, office/hotel lobbies and marketing kiosks.

### Features

#### Mounts Your Tablet to the Floor for Convenient Access

Ideal for displaying menus, directions, instructions, retail information and other important messages, this low-profile security mount lets you install a tablet where your audience can best see it. Quick to assemble and easy to mount, the portable DMTBS911 comes with a bolt-down tamper-resistant base that can be anchored to the floor for a permanent display. The DMTBS911 supports up to 2.2 pounds (1 kilogram).

#### Fits Most Tablets from 9.7 to 10.5 in.

Designed to display your message in information kiosks, office and hotel lobbies, trade shows, conventions and retail settings, the DMTBS911 tablet mount is compatible with most tablets from 9.7 to 10.5 inches. The mount tilts 90 degrees and adjusts to a height between 26.8 and 42.5 inches to provide the most effective viewing angle.

#### Protects Your Device Against Damage, Theft or Tampering

This mount features an anti-theft mechanism with key lock and included keys that helps protect your tablet from unauthorized access. Inside the enclosure are soft anti-skid pads that prevent the device from getting scratched or scuffed up.

### Highlights

- Versatile tablet mount fits select tablets from 9.7 to 10.5 in.
- Locking mechanism with included keys protects your tablet from tampering or theft
- Easy to assemble and install in just a few minutes with the included hardware
- Interior anti-skid pads protect your tablet against scratches and scuff marks
- Adjusts from 26.8 to 42.5 in. high to provide the most comfortable viewing angle

### System Requirements

Tablets from 9.7 to 10.5 in.

### Package Includes

- DMTBS911 Full-Security Tablet Mount Floor Stand
- Installation hardware
- (2) Keys
- Installation instructions

## Specifications

OVERVIEW	
UPC Code	037332278821
Device Compatibility	Tablet
PHYSICAL	
Color	Black; Silver
Material of Construction	Plastic, metal



Powering Business Worldwide

TRIPP LITE  
SERIES

Motion	Full
Mounting Location	Floor
Degrees of Motion	+/-90 Tilt
Minimum Screen Size (in.)	9.7
Minimum Screen Size (cm)	24.6
Maximum Screen Size (in.)	10.5
Maximum Screen Size (cm)	26.7
Maximum Weight Capacity (lbs.)	2.2
Maximum Weight Capacity (kg)	1
Number of Displays	1
Shipping Dimensions (hwd / in.)	14.40 x 28.70 x 2.90
Shipping Dimensions (hwd / cm)	36.58 x 72.90 x 7.37
Shipping Weight (lbs.)	12.60
Shipping Weight (kg)	5.72
Unit Dimensions (hwd / in.)	48.000 x 17.400 x 13.600
Unit Dimensions (hwd / cm)	121.9 x 44.2 x 34.5
Unit Weight (lbs.)	11
Unit Weight (kg)	4.99
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	No
Security Lock	Yes
Height Adjustable	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.