



# Fixed Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWF1323M



### Highlights

- SEE NEW MODEL - DWF1327M
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 13" to 27"
- Supports up to 88 lbs.
- 5-year warranty

### Package Includes

- DWF1323M Fixed Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

### Description

Tripp Lite's VESA-compliant DWF1323M Fixed Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance. Its durable, all-metal frame with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays. It comes pre-assembled for quick and easy installation. For peace of mind, the DWF1323M comes backed by a 5-year warranty.

### Features

- VESA-compliant DWF1323M Fixed Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance
- Durable, all-metal frame with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays
- Pre-assembled for quick and easy installation
- 5-year warranty

## Specifications

OVERVIEW	
UPC Code	037332178732
PHYSICAL	
Color	Black
Material of Construction	Metal
VESA Pattern (mm)	50x50; 75x75; 100x100
Motion	Fixed



Powering Business Worldwide



Mounting Location	Wall
Degrees of Motion	Fixed
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
Shipping Dimensions (hwd / in.)	5.71 x 5.31 x 0.79
Shipping Dimensions (hwd / cm)	14.50 x 13.49 x 2.01
Shipping Weight (lbs.)	1.43
Shipping Weight (kg)	0.65
Unit Dimensions (hwd / in.)	4.720 x 5.500 x 0.600
Unit Weight (lbs.)	1.43
Unit Weight (kg)	0.65
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cord Management	No
Tools Necessary	Yes
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.