

## Swivel/Tilt/Rotate Wall Mount for 37" to 50" TVs and Monitors

MODEL NUMBER: DWM3750S



Suspends a flat-panel television, monitor or other display from the wall. Ideal for home theaters, offices, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWM3750S Swivel/Tilt/Rotate Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall to free up valuable space on your desk, table or workstation. Ideal for home theaters, offices, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 37 to 50 inches.

The full-motion articulating arm adjusts independently with just a touch for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel and -15° to 15° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with soft rubber-feel finish supports up to 40 pounds, tolerates frequent handling, and blends with any décor. Mounts on wood or concrete block with the included hardware. Display cables tuck away inside articulating arm to prevent clutter. Conforms to VESA-compliant displays with hole patterns of 75 x 75 mm, 100 x 100 mm, 200 x 200 mm and 400 x 400 mm.

### Features

#### Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 37 to 50 in.
- Ideal for home theaters, offices, classrooms, boardrooms, hotels, bars and restaurants
- Full-motion articulating arm adjusts independently for angle and height
- Mounting hardware included
- Mounts on wood or concrete block

#### Convenient One-Touch Adjustment

### Highlights

- Fits most flat-panel displays from 37 to 50 in.
- One-touch adjustment for easy viewing from multiple angles
- 180° swivel and -15° to 15° tilt capability
- Durable metal construction
- Supports up to 40 lb.

### Package Includes

- Wallplate
- Spring arm with VESA plate
- Extension arm
- (4) VESA plate adapters
- Hex key, 3 mm
- Hex key, 5 mm
- (4) M4 x 12 mm screws
- (4) M4 x 30 mm screws
- (4) M5 x 12 mm screws
- (4) M5 x 30 mm screws
- (4) M6 x 12 mm screws
- (4) M6 x 30 mm screws
- (4) M8 x 16 mm screws
- (4) M8 x 30 mm screws
- (2) Tension screws
- (8) M8 hex nuts
- (4) Spacers
- (3) Anchor bolts
- (3) Concrete anchor
- (2) Wallplate covers
- (2) Decorative caps
- Level
- Owner's manual



- 180° swivel and -15° to 15° tilt capability provides comfortable viewing from multiple angles

#### Durable Metal Construction

- Supports up to 40 lb.
- Soft rubber-feel finish tolerates frequent handling and blends with any décor
- Display cables tuck inside articulating arm to prevent clutter

#### VESA Compliance

- Conforms with VESA-compliant universal mounting hole patterns

## Specifications

OVERVIEW	
UPC Code	037332190581
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black; Silver
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100; 200x200; 400x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.98
Maximum Screen Size (in.)	50
Maximum Screen Size (cm)	127
Maximum Weight Capacity (lbs.)	40
Maximum Weight Capacity (kg)	18
Min/Max Arm Extension (in.)	2.7" - 24.9"
Min/Max Arm Extension (cm)	6.86 - 62.25
Number of Displays	1
Shipping Dimensions (hwd / in.)	2.95 x 15.94 x 9.13
Shipping Dimensions (hwd / cm)	7.49 x 40.49 x 23.19
Shipping Weight (lbs.)	8.03
Shipping Weight (kg)	3.64
Unit Dimensions (hwd / in.)	6.570 x 2.710 x 24.880



Unit Dimensions (hwd / cm)	16.69 x 6.88 x 63.19
Unit Weight (lbs.)	11.09
Unit Weight (kg)	5.03
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>