

## Tilt Wall Mount for 13" to 27" TVs and Monitors

MODEL NUMBER: DWT1327S



Low-profile mount hangs a flat-panel television, monitor or other display on the wall. Ideal for classrooms, boardrooms, hotels, bars and restaurants. Tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWT1327S Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches. A -15° to +10° tilt capability minimizes glare and provides comfortable viewing from multiple angles. Low-profile mount is concealed behind the display to give a sleek, professional appearance. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 88 lbs (39.9 kgs). Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

### Features

**Mounts Your TV or Monitor to the Wall** Fits most flat-panel televisions, monitors and other displays from 13 to 27 in. Ideal for classrooms, boardrooms, hotels, bars and restaurants. Mounts out of sight behind display for sleek, professional appearance. Mounting hardware included.

**Convenient One-Touch Adjustment** -15° to +10° tilt capability provides comfortable viewing from multiple angles. Improves viewing angles in applications where audience is below the display.

**Durable Metal Construction** Supports up to 88 lbs (39.9 kgs). Scratch-resistant powder-coated finish. Fully assembled for immediate installation.

**VESA Compliance** Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

## Specifications

OVERVIEW	
UPC Code	037332183576
Device Compatibility	Monitor/HDTV

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- Hangs out of sight for a sleek, professional appearance
- -15° to +10° tilt capability for wide range of motion
- Supports up to 88 lbs (39.9 kgs)

### Package Includes

- DWT1327S Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) D5 washers
- (2) Anchor bolts
- (2) Concrete anchors
- Owner's manual

<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-15/+10 Tilt
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
Number of Displays	1
Shipping Dimensions (hwd / in.)	1.00 x 4.80 x 5.20
Shipping Dimensions (hwd / cm)	2.54 x 12.19 x 13.21
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	4.720 x 7.720 x 1.600
Unit Dimensions (hwd / cm)	12 x 19.6 x 4.1
Unit Weight (lbs.)	1.01
Unit Weight (kg)	0.46
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; RoHS3; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.