

EnviroSense2 (E2) Environmental Sensor Module with Temperature and Digital Outputs

MODEL NUMBER: E2MTDO



Monitors ambient temperature conditions and enables remote control of peripherals, including beacons and alarm signals.

Description

The E2MTDO E2 Environmental Sensor Module works with LX Platform devices, including WEBCARDLX, WEBCARDLXE, WEBCARDLXS, PDU3XE-Series PDUs and PDU3E-Series PDUs. By connecting the included USB cable to an LX Platform device, the E2MTDO allows you to remotely monitor ambient temperature conditions in network environments. It also allows you to remotely turn on and off two compatible products, such as beacons and alarm signals.

If temperature values exceed a certain limit or the digital output changes state, it is recorded in the event log of the LX Platform device's PowerAlert® Device Manager interface. The E2MTDO mounts magnetically to most racks and cabinets. Up to three E2 modules can be daisy-chained together. A built-in retention harness secures cable connections to reduce clutter.

Features

Compatible with LX Platform Devices

- Compatible devices include WEBCARDLX, WEBCARDLXE, WEBCARDLXS, PDU3XE-Series PDUs and PDU3E-Series PDUs
- Measures and monitors ambient temperature
- Enables remote control of peripherals, such as beacons and alarm signals
- Supports both AC- and DC-powered peripherals

Easy to Install and Operate

- Attaches magnetically to most racks and cabinets
- Up to 3 E2 modules can be daisy-chained together
- Built-in cable harness reduces clutter
- USB cable included
- Compatible with free downloadable PowerAlert software

Highlights

- Compatible with LX Platform devices
- Easy magnetic mounting to most racks and cabinets
- Up to 3 E2 modules can be daisy-chained together
- Built-in cable harness reduces clutter
- USB cable included

Package Includes

- E2MTDO EnviroSense2 Environmental Sensor Module
- USB cable (A/Micro-B), 3 ft.
- Owner's manual

Specifications



Powering Business Worldwide



UPC Code	037332196279
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
PHYSICAL	
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	1.10 x 4.40 x 6.00
Shipping Dimensions (hwd / cm)	2.79 x 11.18 x 15.24
Shipping Weight (lbs.)	0.29
Shipping Weight (kg)	0.13
Unit Dimensions (hwd / in.)	0.830 x 2.520 x 1.770
COMMUNICATIONS	
Product Compatibility	WEBCARDLX; WEBCARDLXMINI; WEBCARDLXE
FEATURES & SPECIFICATIONS	
Sensing Capability	Temperature
Contact Closure Capability	Contact Closure Output Control
STANDARDS & COMPLIANCE	
Product Compliance	FCC Part 15 Class A (USA); RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.