



Powering Business Worldwide

Universal Wall Bracket for Wireless Access Point with Cover - Right Angle, Steel, White

MODEL NUMBER: ENBRKTCVR



Durable steel bracket mounts your Wi-Fi access point (WAP) high on a wall to protect it from tampering and provide an optimum signal.

Features

Universal Wall-Mount Bracket Secures and Organizes Your Wireless Access Point

Protect your indoor Wi-Fi access point by mounting it high on a wall or ceiling, away from probing hands. This SmartRack® wall bracket is constructed from heavy-duty cold-rolled steel with a durable white powder-coated finish. It's recommended for offices, dorms, hotels, classrooms, small businesses and other indoor areas where you need to keep your WAP secure, organized and out of the way.

Accommodates a Wide Range of WAPs, Including Cisco and Aruba

The ENBRKTCVR fits most access-point bolt patterns and is compatible with Cisco low-profile and universal brackets. It also comes with a T-bar bracket for mounting Aruba and other WAP brands. Hardware is included for equipment installation. Open rear and side cutouts allow easy cable routing and reduce cable clutter. The durable wall bracket comes ready for horizontal or vertical mounting on a wall or ceiling with user-provided hardware.

Locks Securely to Help Prevent Damage, Tampering or Theft

This Wi-Fi access point enclosure features a protective steel cover. It locks securely with the included key to protect its contents against theft, tampering, dust and other contaminants.

Specifications

| OVERVIEW | |
|-------------|--------------|
| UPC Code | 037332214454 |
| Rack Type | Open-Frame |
| PHYSICAL | |
| Color | White |
| Rack Height | 0U |

Highlights

- Designed for Cisco (low-profile and universal), Aruba and most other WAP brands
- Installs high on a wall to protect router/modem/WAP from theft or tampering
- Heavy-duty steel bracket allows an optimum Wi-Fi signal in all directions
- Open rear and side cutouts allow easy access to data and power cabling
- Equipment-mounting hardware included; attaches to wall with user-provided hardware

Applications

- Mount a wireless access point high on a wall or ceiling to protect it from damage, theft or tampering
- Strengthen a wireless signal in another or a distant part of an office

Package Includes

- Wall bracket with cover
- T-bar bracket
- (4) #8-32 screws
- (2) #6-32 screws
- Cable tie
- Key
- Installation guide



Powering Business Worldwide

| | |
|-------------------------------------|-------------------------|
| Maximum Device Depth (cm) | 22.86 |
| Maximum Device Depth (in.) | 9.00 |
| Maximum Device Depth (mm) | 229 |
| Maximum Weight Capacity (lbs.) | 10 |
| Maximum Weight Capacity (kg) | 5 |
| Shipping Dimensions (hwd / in.) | 7.67 x 9.44 x 11.41 |
| Shipping Dimensions (hwd / cm) | 19.50 x 24.00 x 29.00 |
| Shipping Weight (lbs.) | 4.62 |
| Shipping Weight (kg) | 2.10 |
| Unit Dimensions (cm) | 12.8 x 18.7 |
| Unit Dimensions (hwd / in.) | 5.050 x 7.378 x 9.087 |
| Unit Dimensions (hwd / cm) | 12.83 x 18.74 x 23.08 |
| Unit Dimensions (in.) | 5.1 x 7.4 |
| Unit Weight (lbs.) | 3.100 |
| Unit Weight (kg) | 1.41 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.