

Easy Pull Long-Run Display Cable - Type-B Digital PVC Trunk Cable, 25 ft.

MODEL NUMBER: EZB-025



Description

Tripp Lite's EZB-025 25 ft. Easy Pull Digital Trunk cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from HDMI and DVI termination kits that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 25ft. and 100 ft. PVC as well. (Plenum available as custom item). Cable ends are colored-coded yellow to denote Digital applications (VGA trunk cables are green). Cable features 4pr UL20276 individually shielded twisted pairs, one twisted pair and five signal conductors. UL20276 Digital Video Cable supports 1080p.

Features

- Eliminates the need to field terminate HDMI and DVI connectors
- Detachable, screw-on connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Also available in 25ft. and 100 ft. PVC lengths (Plenum cables available upon request)
- UL20276 Digital Video Cable supports 1080p
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Specifications

OVERVIEW

Highlights

- Versatile trunk cable allows for a variety of connection options
- Easily pulls through conduit or confined spaces with included end caps with integrated pull tabs
- UL20276 Digital Video Cable supports 1080p
- Requires a signal booster, such as Tripp Lite's B120-000 (DVI) or B122-000-60 (HDMI)

Package Includes

- Easy Pull Type-B Digital PVC Trunk Cable, 25 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332146861
INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.6
PHYSICAL	
Color	Black; Yellow
Shipping Dimensions (hwd / cm)	2.54 x 19.05 x 25.40
Shipping Dimensions (hwd / in.)	1.00 x 7.50 x 10.00
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
CONNECTIONS	
Side A - Connector 1	DIN 19 PIN (FEMALE)
Side B - Connector 1	DIN 19 PIN (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	DVI; HDMI
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>