

## FireWire® - 3-ft. Firewire IEEE 1394 Gold 6Pin/4Pin Cable

MODEL NUMBER: F007-003-R



### Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. This 3ft. IEEE-1394 Firewire cable has 6-pin male to 4-pin male connectors. It supports data transmission rates of 100~400Mbps and is used most commonly to connect a PC device to an A/V device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity. Premium double-shielded cable with both a braid and a foil shield virtually eliminate crosstalk and reduce EMI/RFI interference. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

### Features

- All Tripp Lite Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

## Specifications

OVERVIEW	
UPC Code	037332019943
INPUT	

### Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity
- Retail Packaging

### System Requirements

- Firewire 1394 device with a 6-Pin connector and a Firewire device with a 4-Pin connector

### Package Includes

- 3-ft. Firewire IEEE 1394 6Pin/6Pin with Gold Connectors



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (ft.)	3
Cable Length (m)	0.91
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / cm)	17.14 x 14.60 x 3.81
Shipping Dimensions (hwd / in.)	6.75 x 5.75 x 1.50
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
<b>CONNECTIONS</b>	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	4 PIN (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>