



Powering Business Worldwide

FireWire® - 3-Port IEEE 1394 Firewire PCI Card

MODEL NUMBER: F201-003

Description

Tripp Lite's IEEE 1394 Firewire 3 Port PCI Card provides your PC with 3 high-speed Firewire ports. Once this card has been installed in your PC you will have a simple and easy way to connect up to three IEEE 1394 Firewire devices. Connecting DV camcorders, hard disk drives, removable drives, scanners, printers, and other 1394 A/V devices including TVs, VCRs and DVDs will be a breeze. Supports data transfer rates up to 400Mb/s. The flexible 3-and-1 design also provides an internal port in case you are using an internal Firewire device such as a hard drive. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Provides 3 active 6-pin Firewire ports
- 3rd port can be internal or external
- Meets IEEE 1394 standards set by the Institute of Electrical and Electronic Engineers
- Provides three fully 1394-compliant ports at 100, 200 and 400 Mbps
- 100% compliant with open host controller interface (OHCI) requirements
- 100% Plug and Play compatible - Devices can be added or removed without restarting the computer
- Supports up to 63 connected Firewire devices
- Peer to Peer communication structure
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Provides 3 active 6-pin Firewire ports
- Meets IEEE 1394 standards set by the Institute of Electrical and Electronic Engineers
- Fully supports version 2.0 of the IEEE 1394 standard for high-speed serial bus communication
- 100% Plug and Play compatible - Devices can be added or removed without restarting the computer
- Supports up to 63 connected Firewire devices

Package Includes

- IEEE 1394 Firewire PCI Card - 3 Port

Specifications

OVERVIEW	
UPC Code	037332096203
Technology	FireWire
CONNECTIONS	
Number of Ports	3
Side B - Connector 1	(3) 6 PIN (FEMALE)
PHYSICAL	
Color	Silver
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	9.50 x 6.50 x 2.50
Shipping Dimensions (hwd / cm)	24.13 x 16.51 x 6.35
Shipping Weight (lbs.)	0.66
Shipping Weight (kg)	0.30
WARRANTY & SUPPORT	



Powering Business Worldwide

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.