

## USB-C to Lightning Sync/Charge Cable (M/M), MFi Certified, White, 2 m (6.6 ft.)

MODEL NUMBER: M102-02M-WH



USB/Lightning cable connects your Apple iPhone, iPad or iPod to the USB-C port on your MacBook, Chromebook or wall/car charger.

### Features

#### USB-C Cable Charges and Syncs Your Latest-Generation iPhone, iPad and iPod

This USB-C sync/charge cable (M/M) connects your iPhone, iPad or iPod to the USB-C port on a computer, MacBook, Chromebook, Ultrabook, car charger or wall charger. It allows you to charge and power your Apple device, while simultaneously syncing and transferring photos, MP3s and other important files at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Reversible C94 Lightning and USB Type-C Plugs Connect in Either Direction

Connect the C94 Lightning plug to your Apple device for charging and synchronizing, and connect the USB-C plug to a USB-C port on a computer or charger. The reversible plugs connect in either direction to ensure you get it on the first try. While the cable is compatible with all USB-C ports, the C94 Lightning connector is designed for optimal charging performance with Apple's 18W USB-C power adapter.

#### MFi-Certified for Broad Device Compatibility

The 20V 3A (60W) Lightning cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

### Highlights

- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers
- C94 Lightning connector compatible with Apple 18W USB-C power adapter
- Integral strain relief helps cable move freely without stress or cracking
- Reversible plugs connect in either direction for immediate no-fuss use

### Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB-C port on your computer or a wall charger up to 2 meters away
- Transfer photos and other important files between an external hard drive and your Apple device
- Pair with an Apple 18W power adapter for optimal charging performance with an iPad Pro, iPad Air or iPhone 8 or later

### System Requirements

- Computer, laptop or charger with USB-C port
- Most current iPhone, iPad and iPod devices

### Package Includes

M102-02M-WH USB-C to Lightning Sync/Charge Cable (M/M), White, 2 m (6.6 ft.)

## Specifications

| OVERVIEW       |                                 |
|----------------|---------------------------------|
| UPC Code       | 037332260871                    |
| Technology     | Lightning: USB 2.0 (High Speed) |
| USB Cable Type | Passive                         |



| <b>PHYSICAL</b>                       |                                     |
|---------------------------------------|-------------------------------------|
| Color                                 | White                               |
| Material of Construction              | PVC                                 |
| Cable Jacket Color                    | White                               |
| Cable Jacket Material                 | PVC                                 |
| Cable Jacket Rating                   | VW-1                                |
| Cable Outer Diameter (OD)             | 4.0mm                               |
| Cable Length (ft.)                    | 6.6                                 |
| Cable Length (m)                      | 2.01                                |
| Cable Length (in.)                    | 78.7                                |
| Shipping Dimensions (hwd / in.)       | 0.91 x 4.57 x 2.36                  |
| Shipping Weight (kg)                  | 0.09                                |
| <b>ENVIRONMENTAL</b>                  |                                     |
| Operating Temperature Range           | 32 to 113 F (0 to 45 C)             |
| Storage Temperature Range             | -40 to 158 F (-40 to 70 C)          |
| Operating Humidity Range              | 10% to 85% RH, Non-Condensing       |
| Storage Humidity Range                | 5% to 90% RH, Non-Condensing        |
| Power Provided to Connected Device(s) | 60W (20V/3A)                        |
| <b>CONNECTIONS</b>                    |                                     |
| Side A - Connector 1                  | USB C (MALE)                        |
| Side B - Connector 1                  | LIGHTNING (MALE)                    |
| Connector Plating                     | Nickel                              |
| Contact Plating                       | Gold                                |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |                                     |
| USB Specification                     | USB 2.0 (up to 480 Mbps)            |
| <b>STANDARDS &amp; COMPLIANCE</b>     |                                     |
| Product Certifications                | MFi                                 |
| Product Compliance                    | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY</b>                       |                                     |
| Product Warranty Period (Worldwide)   | 2-year limited warranty             |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>