

Cat5e 350 MHz Outdoor-Rated Molded (UTP) Ethernet Cable (RJ45 M/M) - Gray, 200 ft. (60.96 m)

MODEL NUMBER: **N007-200-GY**



Highlights

- High Quality Outdoor Rated PVC Jacket
- Molded, Snagless RJ45 Connector

Package Includes

- 200ft Outdoor Rated Cat5e Patch Cable

Features

- UV (Ultra Violet) Resistant Gray PVC Jacket
- CMR, CMX, and UL444 Rated
- EIA/TIA 568-B.2 Compliant
- UL Verified Category 5e
- Molded, Snagless Connectors
- 4pr, Solid Conductors for long distance signal integrity

Specifications

OVERVIEW	
UPC Code	037332135674
Technology	Cat5/5e
POWER	
Power Over Cable (PoC) Support	No
PHYSICAL	
Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	CMR; CMX



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Shielding	UTP
Cable Outer Diameter (OD)	5.5mm
Number of Conductors	4 Pair
Conductor Material	Solid Copper
Cable Length (ft.)	200
Cable Length (m)	61
Cable Length (in.)	2401.6
Cable Length (cm)	6100
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 20.32
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 8.00
Shipping Weight (kg)	2.27
Shipping Weight (lbs.)	5.00
COMMUNICATIONS	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Snagless Connector	No
Antibacterial	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>