


Cat5e 350MHz Bulk Solid-Core PVC Outdoor-Rated Cable - Gray, 1000-ft.

MODEL NUMBER: N028-01K-GY



Highlights

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range -40F to +140F

Package Includes

1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable

Description

Tripp Lite's Outdoor Rated UV Resistant PVC Unshielded Cat5e cable is ideal for connecting to outdoor mounted wireless antennas. 4-pair, 24 AWG, solid conductors, handle long distance runs with low attenuation loss. Jacket is sequentially marked every two feet for easy measuring. Operating temperature range of -40C to +60C. UL1666 Riser and CMX Outdoor ratings. 1000-ft. Pull box; 26lbs. shipping weight. For pre-terminated patch cables, please browse "N007-" in the search box.

Features

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range: -40F to +140F
- 1000-ft. Pull-box, length marked every two feet
- Terminate with Tripp Lite N030-010 Solid wire Cat5e RJ45 plugs

Specifications

OVERVIEW	
UPC Code	037332141491
INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.8
Cable Length (in.)	12000



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (cm)	30480
PHYSICAL	
Cable Jacket Rating	CMX
Cable Shielding	UTP
Color	Gray
Shipping Dimensions (hwd / cm)	22.86 x 37.08 x 38.10
Shipping Dimensions (hwd / in.)	9.00 x 14.60 x 15.00
Shipping Weight (kg)	11.29
Shipping Weight (lbs.)	24.90
Snagless Connector	No
Wire Gauge (AWG)	24
Wire Type	Solid
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
FEATURES & SPECIFICATIONS	
Technology	Cat5/5e
Cable Style	Outdoor Rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>