



Powering Business Worldwide

Eaton 9PX Maintenance Bypass for Select 5kVA to 6kVA 9PX UPS Systems, Hardwired Input/Output, 2 L6-30R Outlets, Rack/Tower/Wallmount

MODEL NUMBER: MBP6K208



Reroutes utility power to keep essential equipment operational while you're servicing or replacing a UPS system.

Features

Compatible with Select Eaton 5kVA/6kVA 9PX UPS Systems

The MBP6K208 works with Eaton's 9PX5K, 9PX6K, 9PX6K-L and 9PX3K3UN UPS systems. The bypass switch lets you service or replace the UPS system without powering down any equipment and risking costly downtime. Power passes directly from a power source to equipment.

Versatile Connection and Installation Options

The MBP6K208 features hardwired input and output connections. Two NEMA L6-30R outlets also allow load connection. You can rear mount the maintenance bypass switch to the back of the UPS. You can also adapt it for tower or wall installation using the included hardware.

Specifications

OVERVIEW	
UPC Code	743172043603
Accessory Type	Bypass Panel (Rack-Mount)
Accessory Class	UPS Accessories
INPUT	
UPS Input Connection Type	Hardwire
OUTPUT	
Individually Controllable Load Banks	No

Highlights

- Isolates UPS from connected loads for maintenance without powering down equipment
- Designed for rear mount in a rack, tower or wall mounting using the included installation hardware
- Compatible with Eaton's 9PX5K, 9PX6K, 9PX6K-L and 9PX3K3UN UPS systems

System Requirements

Compatible with Eaton's 9PX5K, 9PX6K, 9PX6K-L and 9PX3K3UN UPS systems

Package Includes

- MBP6K208 Maintenance Bypass
- Input/output UPS cable set
- (2) Cable glands
- Mounting hardware
- Installation and user manual



Powering Business Worldwide

BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower; Wall-mount
Unit Dimensions (hwd / in.)	5.100 x 7.000 x 4.300
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.